

# Specifications

## Eaton T8S-A-CB

Eaton Basic rack PDU, 1U, C20 input, 3.33 kW max, 110-125V, 12A, 0 ft cord (hardwired), Single-phase, Outlets: (8) 5-15R

### General specifications

<b>PRODUCT NAME</b>	Eaton basic PDU
<b>CATALOG NUMBER</b>	T8S-A-CB
<b>UPC</b>	786685287614
<b>PRODUCT LENGTH/DEPTH</b>	0.0001 in
<b>PRODUCT HEIGHT</b>	0.0001 in
<b>PRODUCT WIDTH</b>	0.0001 in
<b>PRODUCT WEIGHT</b>	0.0001 lb
<b>COMPLIANCES</b>	Contact Manufacturer
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Product specifications

<b>FORM FACTOR</b>	1U
<b>OUTLET CONTROL</b>	No
<b>PHASE</b>	Single-phase
<b>WATTAGE</b>	3.33 kW max
<b>AMPERAGE RATING</b>	12A
<b>INPUT VOLTAGE</b>	110-125V
<b>INPUT CONNECTION</b>	C20
<b>OUTLETS</b>	(8) 5-15R
<b>CORD LENGTH</b>	Hardwired
<b>FREQUENCY RATING</b>	50-60 Hz
<b>OPERATING TEMPERATURE</b>	0° to 60°C (32° to 140°F)

## Resources

<b>CERTIFICATION REPORTS</b>	<a href="#">Eaton RoHS Declaration of Conformity: ePDU G3</a> <a href="#">Eaton RoHS declaration of conformity: ePDU G3</a>
<b>DRAWINGS</b>	<a href="#">Eaton PDU T8S-A-CB technical drawing</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">Eaton ePDU G3 troubleshooting guide</a>
<b>MANUALS AND USER GUIDES</b>	<a href="#">Eaton ePDU G3 operations manual</a> <a href="#">Eaton ePDU G3 installation and connectivity quick start</a> <a href="#">Eaton ePDU G3 replace and configure eNMC module</a> <a href="#">Eaton ePDU G3 1U and 2U installation addendum</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - T8S-A-CB</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

