

Other Hardware

XP8200 Customer Pole Display

The XP8200 Pole Display was designed to blend in beautifully with your POS station. The lack of dip switches make configuration through the provided software a breeze. Featuring OPOS support and several popular emulations, including Epson, CD-5220, and UTC. With larger than industry average characters and featuring an adjustable height stand the XP8200 makes a great addition to any POS station.



Shown with Medium Display

Key Features



Display

Ideal 2-line, 20 character/line Vertical Display for smaller counter spaces



Emulation

10 standard display emulations in addition to OPOS



Adjustable Height

Adjustable height and pitch angles



Multiple Interfaces

USB and RS232 Interfaces

PERFORMANCE

Type	Vacuum Fluorecent Display
Display Pattern	5 x 7 dot matrix
System Interface	USB, RS-232 (dB9)
Brightness	300 - 700 nits
Character Type	95 Alphanumeric and 32 International
Character Size (W x H)	0.207" x 0.366" (5.3mm x 9.3mm)
Character Number	20 per row x 2 rows
Emulations	EPSON ESC/POS, AEDEX, UTC/S, UTC/P, ADM788, DSP800, CD5220, EMAX, LOGIC CONTROL, LD-220

PHYSICAL

Weight	2.3 lbs (1kg)
Dimensions Panel (WxDxH)	8.7" x 2" x 3.4" (221mm x 51mm x 86mm)
Dimensions Base (WxDxH)	8.5" x 4.2" x 1.4" (216mm x 107mm x 36mm)
Extensions	2" x 5.1" (51mm x 130mm)
Viewing Angle	Maximum 90°
Pitch Angle	Maximum 30°
Horizontal Rotation	Maximum 360°
Interface Cable Length	5' (1.7m)
Color	Black

ELECTRICAL

Power	5V, 1A
-------	--------

ENVIRONMENTAL

Temperature	32°F to 114°F (0°C to 45.6°C) operating
Humidity	10% to 95% non-condensing
Shock Resistance	Withstands multiple drops from 3.3' (1m)

WARRANTY EXTENSION AND UPGRADES

ZWE-BMP	2-Year Warranty Extension
ZOE-BMP3	*3-Year Overnight Exchange
ZOE-BMP5	*5-Year Overnight Exchange

*Available in USA and Canada

