

stair TSP1000



- High-Speed Output (180mm/s)
- Large Paper Roll Capacity (Up to 7" Diameter)
- Ticket Stacker Stacks Up to 30 Tickets
- "Drop-In & Print" Paper Loading
- On the Fly Maintenance (Change Cutter or Print Head in Minutes)
- 45mm to 82.5mm Adjustable Paper Width

Versatile Printer with Receipt / Ticket Stacker

The TSP1000 is a specialty POS solution that offers truly outstanding value, reliability, performance and quality.

The TSP1000 high capacity direct thermal printer offers support for up to a 7" diameter paper roll that is ideal for high volume applications. The integrated ticket/document stacker aids in sorting multiple tickets/documents where batch printing is required. With its small footprint, ease of use and high throughput, the TSP1000 easily meets a variety of ticketing application needs. Its low maintenance and reliability make it the ticket printer of choice world-wide.

Perfect for lottery, airline ticketing, large events, ticketing, industrial kitchens, bars and libraries.

Visit www.starmicronics.com to learn more.



Ticket Stacker



Small Footprint



Thick Ticket Support



Large Paper Roll
Capacity



TSP1000 Specifications

Features	The High Volume POS/Lottery Solution!	
	Hardware	Software
	Ultra Fast 34 RPM (180mm/s) "Drop-In & Print" Clamshell Design Adjustable Paper (45mm to 82.5mm) Thick Ticket Support (Up to 0.15mm) Stacks Up to 30 Printed Tickets 7 Inch Paper Roll Capacity (800 ft of Receipt) Small Footprint Swappable Communication Interfaces 1 and 2 Dimensional Barcodes Putty, Gray, Red, Blue Color Housing (Red and Blue are available on special order)	Logo Utility (Store Logos, Coupons, and Graphics) Automatic Second Copy with Raster Driver Memory Switch Configuration / Setup Utility Ethernet Interface Setup Utility StarIO SDK
Connectivity Note: Connections in bold are supported; grayed-out connection types may be supported by special request.	9-Pin Serial 25-Pin Serial Parallel USB Powered USB Ethernet Wireless LAN Dual 9-Pin Serial/USB	Virtual Serial Port to USB Virtual Serial Port to Ethernet Virtual TCP/IP Port
Drivers	Windows® XP Vista (32 bit / 64 bit) Windows 7 (32 bit / 64 bit) Server 2008 (32 bit / 64 bit) CE XP Embedded POS for .NET	USB Vendor Class Linux™ CUPS Mac OS X CUPS
What's Included	TSP1000 Receipt Printer with Cutter and Stacker Paper Stopper Power Switch Cover User Manual Ferrite Core (Parallel, USB, Ethernet Models)	
Optional Accessories	External Power Supply (PS60A) Integrated Buzzer (BU01-24-A) Putty or Gray Color Housing	
Technical Specifications	Print Method : Direct Thermal Print Speed : 180mm/s (34 Receipts Per Minute) Paper Width : 45mm to 82.5mm Paper Thickness : 0.06 - 0.15mm Paper Diameter : Maximum 7" (180mm) Stacker Capacity : Max 30 Sheets Emulation : Star Line Mode, Star Page Mode, ESC/POS™	Power : 24VDC Resolution : 203 dpi MCBF : 60 Million Lines Cutter : 1 Million Cuts Dimensions : W=161mm, H=249mm, D=307mm
Warranty	For US and Canada: 3-Year Limited Warranty, Plus Optional Extended Services Agreement Policies (Extend-A-Star and Swap-A-Star)	
For Further Information	Sales: 1-800-782-7636 x107 Technical Support: 1-800-782-7636 x105	Web: http://www.starmicronics.com

12/27/11

