

GCS62HU

2-Port Cable KVM Switch with HDMI Connections

IOGEAR's GCS62HU 2-Port HD cable KVM switch with audio and HDMI connections combines advanced High Definition Video and USB 2.0 technology. It enables effortless control over 2 devices with HDMI video connections or computers using a single USB keyboard, a USB mouse and a monitor with HDMI connection or HDTV.



Features

- Share a display with HDMI connection, a USB keyboard and mouse, with 2 USB computers
- Separate the Internet and Intranet with the click of a button
- Superior Video Resolution: Up to 1920 x 1200 @60Hz
- Digital Audio support
- HDCP Compliant
- Supports Windows® 7, 8.1, 10, 11, Mac OS® X 9.0+, Linux®, Unix and other USB supported systems
- Works with game consoles
- Port switching via remote switch button, mouse or hotkeys
- Hotkeys allows independent KVM and audio switching between computers
- Includes 2.1 stereo sound and microphone support
- IOGEAR's DynaSync² reads and remembers the monitor's parameters (EDID) so there is no delay or change of video resolution when switching between, or booting computers
- USB 2.0 Peripheral Sharing via mouse port. Connect a powered USB Hub to expand your USB connectivity³
- USB mouse and keyboard emulation for error-free boot-up and instantaneous recognition when switching computers
- Power-On Detection – If one of the computers is powered off, it will automatically switch to the next powered-on computer
- Re-programmable hotkey activation for keyboards without a scroll lock key
- Keyboard emulation can be disabled to support gaming keyboard's special keys
- Mouse emulation can be disabled to support mice with special keys
- Mac and Sun keyboard support
- Firmware upgradeable
- Plug-n-play; no software required

¹IOGEAR's DynaSync provides the EDID support for Windows® 7

²Mouse emulation must be disabled for this feature to function correctly

Requirements

Console:

www.iogear.com

Package Contents

- 1 x 2-Port HD Cable KVM Switch



- 1 x HDMI display
- 1 x standard 104 key wired USB keyboard
- 1 x standard 2 or 3 button wired USB mouse

- 1 x Installation Guide
- 1 x Warranty Card

Computers:

- 1 x HDMI port
- 2 x USB ports

Operating Systems:

- Windows® 7, 8.1, 10, 11
- Mac OS® X 9.0+
- Oracle® Solaris
- Linux®, Unix and other USB supported systems*

**Additional drivers and support may be needed*

***IOGEAR's Display Emulation Technology provides the EDID support for Windows® 7*

Specifications

| FUNCTION | GCS62HU | DIMENSIONS | GCS62HU |
|-----------------------|--|--------------------------|-----------------|
| Computer Connections | | Unit Dimensions | |
| Direct | 2 | Height | 0.98" (2.5cm) |
| Console Connection | 1 | Depth | 2.56" (6.5 cm) |
| Port Selection | Hotkey, Remote Pushbutton or Mouse Switching | Width | 3.15" (8 cm) |
| Console Connectors | | Unit Package Dimensions | |
| Monitor | 1 x HDMI Type A Female | Height | 9.25" (23.49cm) |
| Keyboard | 1 x USB Type A Female | Width | 6.5" (16.51cm) |
| Mouse | 1 x USB Type A Female | Depth | 2.75" (6.99cm) |
| Audio | 1 x 3.5mm Mini Stereo Jack Female (Green) | Master Carton | |
| Microphone | 1 x 3.5mm Mini Stereo Jack Female (Pink) | Height | 9.5" (24.13cm) |
| CPU Connectors | | Width | 16" (40.64cm) |
| Monitor | 2 x HDMI Type A Male | Depth | 7.5" (19.05cm) |
| Keyboard | 2 x USB Type A Male (Purple) | Master Carton Qty. | 6 |
| Mouse | 2 x USB Type A Male (Black) | Weight | |
| Audio | 2 x 3.5mm Mini Stereo Jack Male (Green) | Master Carton Wt. | 8lbs |
| Microphone | 2 x 3.5mm Mini Stereo Jack Male (Pink) | Unit Pack Wt. | 1.20lbs |
| LEDs | | Unit Wt. | .94lbs |
| Physical Properties | | | |
| On Line | 2 x Green | Unit Weight | .94lbs |
| Emulation | | Unit Weight with package | 1.20lbs |
| Keyboard | USB | | |
| Mouse | USB | | |
| Video Resolution | Up to 1920x1200@60Hz | | |
| Scan Interval | 3, 5, 10 , 20 seconds (Default 5 seconds) | | |
| Environment | | | |
| Operation Temperature | 0-50C | | |
| Storage Temperature | -20-60C | | |
| Humidity | 0-80% RH; Non-condensing | | |
| Housing | | | |
| Case | Plastic | | |
| Cable Length | 4ft KVM Cables; 6ft Remote Switch Cable | | |