



KRAMER

900N

Stereo Power Amplifier (10 Watts per Channel)

| Speakers



The 900N is a high-performance power amplifier for balanced or unbalanced stereo audio signals. Either input can deliver a speaker output of 10 watts RMS power per channel into a 4Ω load

FEATURES

High Efficiency - Class D operation

S/N Ratio - 55dB

Controls - Volume knob, On LED

Special Note - Before turning on the 900N, make sure the volume is turned down to the minimum

Compact Kramer TOOLS™ - 3 units can be rack mounted side-by-side in a 1U rack space with the recommended rack adapter



KRAMER

TECHNICAL SPECIFICATIONS

INPUTS:	1 unbalanced stereo audio on RCA connectors; 1 balanced stereo audio on a 5-pin terminal block connector
OUTPUT:	1 stereo loudspeaker output on a 4-pin terminal block connector
OUTPUT POWER:	10W RMS per channel into a 4Ω load
OUTPUT MUSIC POWER:	35W RMS per channel into a 4Ω load
BANDWIDTH (-3dB):	24kHz
S/N RATIO:	55dB
CONTROLS:	Gain: -40dB to +19dB until the compression threshold
COUPLING:	Input: AC; speakers out: DC
AUDIO THD + NOISE:	0.5% @1kHz
AUDIO 2nd HARMONIC:	0.04% @1kHz
POWER CONSUMPTION:	12V DC, 2.1A
INCLUDED ACCESSORIES:	Power supply, mounting bracket
Product Dimensions	12.00cm x 7.15cm x 2.44cm (4.72" x 2.81" x 0.96") W, D, H
Product Weight	0.2kg (0.4lbs) approx
Shipping Dimensions	23.20cm x 13.60cm x 10.00cm (9.13" x 5.35" x 3.94") W, D, H
Shipping Weight	0.6kg (1.3lbs) approx

