



Quam

C5/BU/W

CEILING MOUNTED

8" O.D. Loudspeaker with a 5 oz. magnet, 5W-25/70V Transformer, Screw-Mount Baffle

GENERAL DESCRIPTION

The C5/BU/W consists of an 8C5PAX - 8" O.D. dual cone loudspeaker with a 5 oz. magnet, TBLU - 5W-25/70V transformer, and a BR8W - round, screw-mount baffle in a white powder coat finish.

INTENDED USE - Indoor Environment

Program Material | Signal tones, voice, and music

AUDIO SPECIFICATIONS

Average Sensitivity	92 dB SPL, 1W/ 1M
Loudspeaker Power Rating	12W RMS, EIA 426A Standard
Maximum Power Rating	15W @ 8 Ohms
Calculated Output	99 dB SPL, 5W/ 1M
Magnet Type & Weight	BeFe Ceramic, 5 oz. Nominal
Frequency Response	65 Hz - 17 kHz EIA 426A Standard
Nominal Coverage Angle	100° Included Angle, -6 dB / 2 kHz, Half space
Audio Connection	7" Color-Coded Leads

RECOMMENDED QUAM COMPONENTS

Enclosures	ERD-8, ERD8U
Mounting Device	SSB-2, SSB-3, SSB-7

