

CEILING LOUDSPEAKER

Quam C5/B25/W

C5/B25/W consists of an 8" O.D., dual cone loudspeaker with a 5 oz. magnet, a 4W, 25V transformer, and a round, screw-mount baffle with a white, powder coat finish. It is designed for paging/intercom applications that require a high efficiency speaker and clear, accurate sound.



APPLICATION	Intended Use: Program Material:	Indoor environment Signal tones, voice and music
AUDIO PERFORMANCE	Average Sensitivity: Loudspeaker Power Rating: Maximum Power Rating: Calculated Output: Magnet Type & Weight: Frequency Response: Nominal Coverage Angle: Audio Connection:	92 dB SPL, 1W/ 1M 12W RMS, EIA 426A Standard 15W @ 8 Ohms 98dB SPL, 4W/ 1M BeFe Ceramic, 5 oz. Nominal 65Hz - 17 kHz, EIA 426A Standard 100° Included Angle, -6dB/2kHz, Half Space 7", Color-coded, Pre-tinned Leads
COMPONENT	Dimensions: Combined Weight: Loudspeaker Model: Loudspeaker Specs: Transformer: Baffle: Finish:	12 7/8" (Diameter) x 2 1/2" (H) 3.5 lbs. 8C5PAX 8" O.D. loudspeaker, 5 oz. magnet TBL25: 4W, 25V, with 5 taps (0.25W, 0.50W, 1.0W, 2.0W, 4.0W) BR8W: round, steel, screw-mount White powder coat finish
RECOMMENDED QUAM COMPONENTS	Enclosures: Mounting Supports:	ERD-8, ERD8U SSB-2, SSB-3, SSB-7

