

SURFACE MOUNT LOUDSPEAKER

Quam SYSTEM 3/VC

SYSTEM 3/VC is a complete loudspeaker system consisting of an 8" O.D., dual cone loudspeaker and a 5W, 25/70V transformer with screwdriver or knob adjusted volume control mounted on a square, screw mount, steel baffle attached to a slanted, steel, open back, surface mount enclosure. The entire unit has a white, powder coat finish.



APPLICATION	Intended Use: Program Material: Installation:	Indoor environment Signal tones, voice and music Vertical surface mount, downward firing
AUDIO PERFORMANCE	Average Sensitivity: Loudspeaker Power Rating: Maximum Output: Calculated Output: Magnet Type & Weight: Frequency Response: Nominal Coverage Angle: Audio Connection:	92dB SPL, 1W/1M 12W RMS, EIA 426A Standard 15W @ 8 Ohms 99dB SPL, 5W/1M BeFe Ceramic, 5 oz. Nominal 65Hz - 17kHz EIA, 426A Standard 100° Included Angle, -6dB/2kHz, Half Space 7", Color-coded, Pre-tinned Leads
COMPONENT	Dimensions: Weight: Loudspeaker: Transformer: Baffle: Backbox: Finish: Other:	11 3/8" (H) x 11 5/8" (W) x 5 5/16" (D) 5 lbs. 8C5PAX TBLU: 5W, 25/70V, with 5 taps (0.31W, 0.63W, 1.25W, 2.5W, 5.0W) BS8W SE2WVP with four (4) 8-32 threaded inserts White powder coat Screwdriver or knob adjusted volume control accessible through hole in bottom center of enclosure

