


960H Color or Standard BW In-Wall Camera

- CVC675** 3.6mm lens, color
CVC75 3.6mm lens, BW

Features

- Fits into a single gang electrical box (included)
- Brushed stainless steel faceplate
- Lens options available
- 700 TV lines of resolution
- 5 year warranty

960



Specifications

	CVC675	CVC75
Image Sensor	1/3" Sony Super HAD II™ color CCD	1/3" BW CCD
Resolution.....	700 TV lines	420 TV lines
Minimum Illumination.....	0.001 lux (sense-up on)	0.02 lux
Effective Pixels	976 (H) x 494 (V)	512 (H) x 492 (V)
Scanning System.....	2:1 interlace	2:1 interlace
Angle of View.....	Horizontal: 72° / Vertical: 53°	Horizontal: 72° / Vertical: 53°
Outputs / Connection.....	Video - RCA, Power - DC jack	Video - BNC, Power - DC jack
Scanning Frequency.....	15.75kHz (H) / 60Hz (V)	15.75kHz (H) / 60Hz (V)
Electronic Shutter Speed.....	Auto: 1/60 sec. – 1/50,000 sec.	Auto: 1/60 sec. – 1/50,000 sec.
Synchronization	Internal	Internal
Video Output Level.....	1.0Vp-p / 75 ohms	1.0Vp-p / 75 ohms
Video S/N Ratio	Greater than 52dB	More than 48dB
Housing	Stainless steel	Stainless steel
Operating Temperature/		
Humidity.....	14° F – 122° F / within 90% RH	14° F – 122° F / within 90% RH
Power Consumption	110mA	130mA
Power Supply	12VDC regulated (UL & CSA listed power supply included)	12VDC regulated (UL & CSA listed power supply included)
Dimensions.....	2.75" (W) x 4.25" (H) x 2.75" (L)	2.75" (W) x 4.25" (H) x 2.75" (L)
Weight	3.45 oz.	3.45 oz.

Optional Lenses

CVC6752.2.....2.2mm lens	CVC6758.....8mm lens
CVC6752.5.....2.5mm lens	CVC67512.....12mm lens
CVC6752.9.....2.9mm lens	CVC67516.....16mm lens
CVC6756.....6mm lens	