

Specifications

Eaton T2235-A2-CNB09S

Eaton ATS rack PDU, 1U, (2) 5-20P input, 1.92 kW max, 110-125V, 16A, 9 ft. cord, Single-phase, Outlet: (8) 5-20R

General specifications

PRODUCT NAME	Eaton ATS PDU
CATALOG NUMBER	T2235-A2-CNB09S
UPC	786685287324
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	23 in
PRODUCT WIDTH	13.5 in
PRODUCT WEIGHT	15 lb
WARRANTY	3 year
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	UL Listed

Physical

MOUNTING DIRECTION	Horizontal
COLOR	Black
FORM FACTOR	1U
OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)

Electrical output

OUTLETS	(8) 5-20R
CIRCUIT BREAKER	1P 20A
OUTLET CONTROL	No

Resources

MANUALS AND USER GUIDES	Eaton T2235 series eATS ePDU
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - T2235-A2-CNB09S

Electrical input

INPUT CONNECTION	(2) 5-20P
CORD LENGTH	9 ft
WATTAGE	1.92 kW max
AMPERAGE RATING	16A
INPUT VOLTAGE	110-125V
PHASE	Single-phase
FREQUENCY RATING	50-60 Hz

Additional specifications

SERIES	eATS
---------------	------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

