

Specifications

Eaton TPC115-3538

Eaton REPO rack PDU, 1U, 1.92 kW max,
110-125V, 16A, 9 ft cord, Single-phase

General specifications

PRODUCT NAME	Eaton REPO Rack PDU
CATALOG NUMBER	TPC115-3538
PRODUCT LENGTH/DEPTH	0.01 in
PRODUCT HEIGHT	0.01 in
PRODUCT WIDTH	0.01 in
PRODUCT WEIGHT	0.01 lb
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	Contact Manufacturer

Physical

MOUNTING DIRECTION Horizontal

COLOR Black

FORM FACTOR 1U

Electrical input

CORD LENGTH 9 ft

WATTAGE 1.92 kW max

AMPERAGE RATING 16A

INPUT VOLTAGE 110-125V

PHASE Single-phase

FREQUENCY RATING 50-60 Hz

Electrical output

CIRCUIT BREAKER 1P 20A

OUTLET CONTROL No

Additional specifications

OPERATING TEMPERATURE 0° to 60°C (32° to 140°F)

SERIES RE

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - TPC115-3538](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.