

## 2m DVI-D Dual Link Cable – M/M

StarTech ID: *DVIDDMM2M*



The DVIDDMM2M 2m DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 2m DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

### Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

### Technical Specifications

Warranty	Lifetime
Number of Conductors	24
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	2
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-D (25 pin) Male
Connector B	1 - DVI-D (25 pin) Male
Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	2 m [6.6 ft]
Cable OD	8.6 mm [0.3 in]
Product Weight	193 g [6.8 oz]
Package Quantity	1
Shipping (Package) Weight	198
Included in Package	1 - 2m DVI-D Dual Link Digital Video Monitor Cable - M/M

### Certifications, Reports and Compatibility

