



Ultra Series: 720+ TVL

The Ultra series boasts cameras that are 720+ TVL. Many offer True Day/Night with DWDR (Digital Wide-Dynamic Range) and OSD (On Screen Display) menu which provides a whole range of additional features and configurations to give you the best possible image!

	ED700	Indoor Day/Night, 3.6mm, 720+ TVL, 3-axis, 12VDC
	ED710	Indoor True Day/Night with DWDR, 2.8-12mm, 720+ TVL, 3-Axis, OSD, Dual Voltage
	ED730	Indoor True Day/Night with DWDR IR Dome 720+ TVL, 2.8-12mm, 3-Axis, OSD, 100 Ft IR Range, Dual Voltage
	EHD700	Outdoor True Day/Night with DWDR, 2.8-12mm, 720 TVL, OSD, 3-Axis, IP66 Weather Resistant, Flush/Surface Mount, Dual Voltage, Wall Mount with BA-EHD2
	EHD730	Outdoor True Day/Night with DWDR IR Dome, 2.8-12mm, 720 TVL, OSD, 3-Axis, IP66 Weather Resistant, Flush/Surface Mount, Heater, 100 Ft IR Range, Dual Voltage, Wall Mount with BA-EHD2
	EMD700B (Black)	Outdoor Day/Night with DWDR Mini Vandal/Mobile Dome, 3.6mm Lens, 720 TVL, IP67 Waterproof, 12VDC, Works up to -40 Degrees!
	EMD700W (White)	
	EMC700	Outdoor Simple Day/Night with DWDR Mini Bullet, 3.6mm, 720+ TVL, IP67 Waterproof, OSD, 12VDC
	EQ700	True Day Night with DWDR Box Cam, Ultra Low Light, 720+ TVL, OSD, C/CS Mount, Dual Voltage (Lens not included)
	EZ700B (Black)	Outdoor Mini Day/Night with DWDR, 3.5-16mm, 720+ TVL, IP67 Weather Resistant, Dual Voltage, Cable through Mount
	EZ700W (White)	
	EZ730B (Black)	Outdoor True Day/Night with DWDR IR Bullet, 2.8-12mm, 720+ TVL, OSD, IR Range 80+ Ft, IP66 Weather Resistant, Dual Voltage, Covert IR
	EZ730W (White)	
	EZ750	Outdoor True Day/Night with DWDR IR Day/Night Bullet, 2.8-12mm, 720+ TVL, OSD, IR Range 160+ Feet, IP67 Waterproof, Dual Voltage,
	EM700P1	Indoor Day/Night with DWDR Mini Board Camera, 3.7mm cone, 720+ TVL, Board, OSD, 12VDC
	EM700P3	Indoor Day/Night with DWDR Mini Board Camera, 3.7mm pinhole, 720+ TVL, Board, OSD, 12VDC
	EM700P4	Indoor Day/Night with DWDR Mini Board Camera, 4.3mm cone, 720+ TVL, Board, OSD, 12VDC

