

Lexmark C792 Family color laser printers



Flexible, robust color printing

Models



Lexmark C792 Family

The Lexmark C792 Family color laser printers combine robust design with brilliant color printing, exceptional media handling, flexible finishing options and an intuitive color touch screen.

-  Color
-  Touch screen
-  Solutions
-  Up to 50 ppm
-  Duplex*
-  Network

* Duplex not available on C792e model.

Other available models:

Lexmark C792e: Enjoy the benefits of workgroup color laser printing through a robust design combined with exceptional media handling and an intuitive color touch screen.

Lexmark C792de: Includes duplex

Lexmark C792dte: Includes duplex and additional 550-sheet drawer

Lexmark C792dhe: Includes duplex, hard disk, three additional 550-sheet drawers, 1GB memory and caster base

LEXMARK
TM

Lexmark C792 Family: key features



Lexmark C792dhe color laser printer shown with optional finisher

Features that help you optimize your work




1) Intuitive color touch screen

The 4.3-inch color touch screen allows you to operate your printer with ease and confidence through smart and intuitive navigation, easy access to workflow solutions and shortcuts, and the ability to preview your documents and print jobs at the device.



2) Flexible output options

Choose from four output options, including a five-bin mailbox, an offset stacker, a staple finisher, and a staple with hole punch finisher.



4) Lexmark solutions

Reduce unnecessary printing and simplify work processes through solutions applications preloaded on your device. Choose additional Lexmark solutions to fit your unique workflow needs.



5) Expandable input

Print on multiple paper types and boost total capacity up to 3,200 sheets.



6) Long-lasting toner

The Lexmark Extra High Yield Print Cartridge delivers up to 20,000* pages, reducing interventions, cartridge waste and cost.

7) Eco-friendly features

Easy-to-access features make it easy to print responsibly, including Eco-Mode to reduce paper and toner consumption, and the Sleep button and Hibernate Mode to help you save energy.

Lexmark C792 Family: overview



Robust Color Printing

Designed for medium to large workgroups, the Lexmark C792 Family meets the demands of your busy color-printing environment. Vibrant, professional-quality output and the ability to print on a wide variety of media allow you to do more color printing in-house. With the advanced color laser technology of the C792 Family, you'll get excellent, consistent color from the first page to the last.

- Lexmark Extra High Yield Print Cartridge available, offering yields of up to 20,000* pages
- Print and duplex** speeds as fast as 50 ppm in both black and color
- PANTONE® calibration for consistent color tones
- Named Color Replacement for easy color matching
- Lexmark Color Care Technology to manage color usage and control costs
- Instant warm-up fuser to help reduce energy consumption and improve time to first page



Flexibility

Choose from a variety of models to best serve your needs. Select from a number of expandability options and finishing features you would expect from more expensive products.

- Ultra-reliable paper feeding to support diverse media, including card stock, labels, UV-resistant outdoor media, banner media and more
- Robust output options, including a five-bin assignable mailbox, an offset stacker, a staple finisher, and a staple with hole punch finisher
- Input capacity expandable to up to 3,200 sheets with the high-capacity feeder and an extra drawer
- Connectivity and application solution cards allow integration into most IT environments



Easy and Intuitive

The Lexmark C792 Family is designed for easy operation and maintenance.

- 4.3-inch color touch screen provides audible feedback to make completing tasks intuitive
- Print Preview features help you select documents or specific pages within a document
- Directional lights on the device provide visual cues to guide you through tasks and maintenance operations
- Ability to change settings such as duplex** or stapling at the device
- Available device fleet management software
- Sleep button and Hibernate Mode, helping to reduce energy costs

*Average continuous black or composite CMY declared cartridge yield in accordance with ISO/IEC 19798.

** Duplex not available on C792e model.

Lexmark C792 Family: solutions

Print Less. Save More.

Print less? This may seem like a surprising message for a company dedicated solely to printing. But when you consider that businesses spend on average up to 6% of their revenue on printing and that active print management can cut office print costs by up to 30%*, it makes a lot of sense. Lexmark products, solutions and services provide innovative ways to save you time, drive down costs and reduce your impact on the environment. We are committed to helping you print less and save more.



Solutions

Save time and money through solutions

Reduce unnecessary printing and simplify work processes with Lexmark solutions. The C792 Family features the Lexmark Embedded Solutions Framework (eSF), our platform that enables you to add a wide range of software applications directly onto the device. Solutions are designed with your productivity in mind, helping you streamline—or even eliminate—paper intensive business processes.

Below are solutions that come preloaded on the C792 Family. A diverse portfolio of additional Lexmark solutions is available to help accommodate your workflow needs.



Forms and Favorites

Eliminate waste and inefficiencies associated with preprinted forms. Store frequently printed forms, marketing materials or other documents online, then print them on demand.



Background and Idle Screen

Change the touch screen background to your corporate logo, a unique message, or select one of the four screens that are preloaded on the device.



Eco-Settings

Choose from multiple print settings that help reduce energy, paper and toner consumption.



Change Language**

Easily switch the language displayed on the touch screen – 18 languages supported.



Showroom

Display a customizable, scrolling slideshow on the color touch screen to promote your business or products, or to communicate important messages to your customers or employees.

Lexmark C792 Family: highlights

Make a lasting impression with award-winning color

The documents you print define an important image – yours. That's why Lexmark color lasers help businesses be more productive and stand out with vibrant color. With the ability to print professional quality color in-house, you can add instant impact and save costs by virtually eliminating the need to outsource print jobs. Lexmark also offers a host of color-access and control tools to manage costs.



Functions



The right touch

The Lexmark e-Task color touch screen is a key access point to your printer. The customizable 4.3-inch interface gives you the ability to preview thumbnails of documents prior to printing, as well as change print jobs at the device. You can even view, select and print specific pages within a document directly from the touch screen. Its easy-to-use, intuitive navigation provides fast access to the functions, shortcuts and workflows you use most. New interactive sensory features provide audible feedback, helping to guide you through each operation, confirming a touch has registered and indicating an action is transpiring.



Protecting your information

From the data traveling through your network to the pages being printed, Lexmark's innovative security controls give you peace of mind that your valuable corporate data is protected at every stage.

- Cutting-edge user authentication and authorization controls, including LDAP, help protect your device and data
- Card reader option to add an extra layer of security
- Hard disk encryption protects sensitive data on the disk drive

- Automatic, scheduled or manual disk wiping
- IPSec, SNMPv3 and 802.1x network security supported
- Security-audit logging to help track and identify security risks




True Image Always

Lexmark is dedicated to designing and manufacturing products that deliver exceptional quality and reliable performance. Maximize the return on your investment, extend the service life of your Lexmark printing equipment and make a lasting impression by always insisting on Lexmark Genuine Supplies, Service and Parts. Lexmark C792 Family color laser printers are backed by a one-year base warranty. For further protection against unexpected expenses or downtime, extended warranty offerings are available.

Lexmark C792 Family: ordering information

Lexmark C792de



550-Sheet Drawer




550-Sheet Drawer
2,000-Sheet High-Capacity
Feeder




Spacer




Caster Base (Required for floor
standing configuration)




500-Sheet Offset Stacker



500-Sheet Staple Finisher



500-Sheet Staple Punch Finisher



5-Bin Mailbox

Standard
 Optional



Eco-responsible printing

Printing responsibly means everyone wins – your business, your budget and the environment. Lexmark's award-winning products are designed for ease of use, high quality output and reliable performance, with innovative capabilities that help you minimize the number of cartridges you use over the life of the printer and conserve paper and energy. Our goal is to design, package and deliver innovative products and solutions in an environmentally responsible manner.

Lexmark C792 Family: ordering information

Lexmark C792e

Part #	Model
47B0000	Lexmark C792e
Part # Laser Toner/Print Cartridge	
C792X1KG	C792 Black Extra High Yield Return Program Print Cartridge
C792X1CG	C792 Cyan Extra High Yield Return Program Print Cartridge
C792X1MG	C792 Magenta Extra High Yield Return Program Print Cartridge
C792X1YG	C792 Yellow Extra High Yield Return Program Print Cartridge
C792A1KG	C792 Black Return Program Print Cartridge
C792A1CG	C792 Cyan Return Program Print Cartridge
C792A1MG	C792 Magenta Return Program Print Cartridge
C792A1YG	C792 Yellow Return Program Print Cartridge
C792X2KG	C792 Black Extra High Yield Print Cartridge
C792X2CG	C792 Cyan Extra High Yield Print Cartridge
C792X2MG	C792 Magenta Extra High Yield Print Cartridge
C792X2YG	C792 Yellow Extra High Yield Print Cartridge
C792X77G	C792, X792 Waste Toner Bottle
25A0013	Staple Cartridges (3 pack)
Part # Paper Handling	
47B0110	C792, X792 550-Sheet Drawer

In the box

Lexmark C792e color laser printer, Up to 11,000*-page Cyan, Magenta, Yellow Starter Print Cartridges, Up to 8,500*-page Black Starter Print Cartridge, Software and Documentation CD, Power Cord(s), Setup Guides (network and local attachment), Statement of limited warranty, Lexmark Cartridge Collection Program information

Lexmark C792de

Part #	Model
47B0001	Lexmark C792de
Part # Laser Toner/Print Cartridge	
C792X1KG	C792 Black Extra High Yield Return Program Print Cartridge
C792X1CG	C792 Cyan Extra High Yield Return Program Print Cartridge
C792X1MG	C792 Magenta Extra High Yield Return Program Print Cartridge
C792X1YG	C792 Yellow Extra High Yield Return Program Print Cartridge
C792A1KG	C792 Black Return Program Print Cartridge
C792A1CG	C792 Cyan Return Program Print Cartridge
C792A1MG	C792 Magenta Return Program Print Cartridge
C792A1YG	C792 Yellow Return Program Print Cartridge
C792X2KG	C792 Black Extra High Yield Print Cartridge
C792X2CG	C792 Cyan Extra High Yield Print Cartridge
C792X2MG	C792 Magenta Extra High Yield Print Cartridge
C792X2YG	C792 Yellow Extra High Yield Print Cartridge
C792X77G	C792, X792 Waste Toner Bottle
25A0013	Staple Cartridges (3 pack)
Part # Paper Handling	
47B0110	C792, X792 550-Sheet Drawer

In the box

Lexmark C792de color laser printer, Up to 11,000*-page Cyan, Magenta, Yellow Starter Print Cartridges, Up to 8,500*-page Black Starter Print Cartridge, Software and Documentation CD, Power Cord(s), Setup Guides (network and local attachment), Statement of limited warranty, Lexmark Cartridge Collection Program information

Lexmark C792dte

Part #	Model
47B0002	Lexmark C792dte
Part # Laser Toner/Print Cartridge	
C792X1KG	C792 Black Extra High Yield Return Program Print Cartridge
C792X1CG	C792 Cyan Extra High Yield Return Program Print Cartridge
C792X1MG	C792 Magenta Extra High Yield Return Program Print Cartridge
C792X1YG	C792 Yellow Extra High Yield Return Program Print Cartridge
C792A1KG	C792 Black Return Program Print Cartridge
C792A1CG	C792 Cyan Return Program Print Cartridge
C792A1MG	C792 Magenta Return Program Print Cartridge
C792A1YG	C792 Yellow Return Program Print Cartridge
C792X2KG	C792 Black Extra High Yield Print Cartridge
C792X2CG	C792 Cyan Extra High Yield Print Cartridge
C792X2MG	C792 Magenta Extra High Yield Print Cartridge
C792X2YG	C792 Yellow Extra High Yield Print Cartridge
C792X77G	C792, X792 Waste Toner Bottle
25A0013	Staple Cartridges (3 pack)
Part # Paper Handling	
47B0110	C792, X792 550-Sheet Drawer

In the box

Lexmark C792dte color laser printer, Up to 11,000*-page Cyan, Magenta, Yellow Starter Print Cartridges, Up to 8,500*-page Black Starter Print Cartridge, 550-Sheet drawer, Software and Documentation CD, Power Cord(s), Setup Guides (network and local attachment), Statement of limited warranty, Lexmark Cartridge Collection Program information

Lexmark C792dhe

Part #	Model
47B0003	Lexmark C792dhe
Part # Laser Toner/Print Cartridge	
C792X1KG	C792 Black Extra High Yield Return Program Print Cartridge
C792X1CG	C792 Cyan Extra High Yield Return Program Print Cartridge
C792X1MG	C792 Magenta Extra High Yield Return Program Print Cartridge
C792X1YG	C792 Yellow Extra High Yield Return Program Print Cartridge
C792A1KG	C792 Black Return Program Print Cartridge
C792A1CG	C792 Cyan Return Program Print Cartridge
C792A1MG	C792 Magenta Return Program Print Cartridge
C792A1YG	C792 Yellow Return Program Print Cartridge
C792X2KG	C792 Black Extra High Yield Print Cartridge
C792X2CG	C792 Cyan Extra High Yield Print Cartridge
C792X2MG	C792 Magenta Extra High Yield Print Cartridge
C792X2YG	C792 Yellow Extra High Yield Print Cartridge
C792X77G	C792, X792 Waste Toner Bottle
25A0013	Staple Cartridges (3 pack)
Part # Paper Handling	
47B0110	C792, X792 5-Bin Mailbox

In the box

Lexmark C792dhe color laser printer, Up to 11,000*-page Cyan, Magenta, Yellow Starter Print Cartridges, Up to 8,500*-page Black Starter Print Cartridge, Hard disk, 3x 550-Sheet drawers, Caster base, Software and Documentation CD, Power Cord(s), Setup Guides (network and local attachment), Statement of limited warranty, Lexmark Cartridge Collection Program information

Lexmark C792 Family: product specifications

	Lexmark C792e	Lexmark C792de	Lexmark C792dte	Lexmark C792dhe
Printing				
Print Technology		Color Laser		
Print Speed (Letter, Black): Up to		50 ppm		
Print Speed (Letter, Color): Up to		50 ppm		
Time to First Page (Black)		As fast as 8 seconds		
Time to First Page (Color)		As fast as 8.5 seconds		
Print Resolution, Black		1200 x 1200 dpi, 4800 Color Quality (2400 x 600 dpi)		
Print Resolution, Color		1200 x 1200 dpi, 4800 Color Quality (2400 x 600 dpi)		
Memory, Standard	512 MB	512 MB	512 MB	1024 MB
Memory, Maximum		1536 MB		
Hard Disk	Option available	Option available	Option available	Included in configuration
Print Noise Level, Operating		52 dBA		
Noise Level, Idle		29 dBA		
Maximum Monthly Duty Cycle: Up to		150000 pages per month		
Recommended Monthly Page Volume		2500 - 17000 pages		
Supplies				
Supplies Yield	6,000*-page (CMYK) Print Cartridges, 20,000*-page (CMYK) Extra High Yield Print Cartridges			
(*Average continuous black or continuous composite CMY declared cartridge yield up to this number of standard pages in accordance with ISO/IEC 19798.)				
Paper Handling				
Paper Handling Standard	500-Sheet Output Bin, 100-Sheet Multipurpose Feeder, 550-Sheet Input Tray	500-Sheet Output Bin, Integrated Duplex, 100-Sheet Multipurpose Feeder, 550-Sheet Input Tray	500-Sheet Output Bin, Integrated Duplex, 100-Sheet Multipurpose Feeder, 550-Sheet Drawer, 550-Sheet Input Tray	500-Sheet Output Bin, Integrated Duplex, 100-Sheet Multipurpose Feeder, 550-Sheet Input Tray, 3 x 550-Sheet Drawers
Paper Handling Optional	5-Bin Mailbox, 550-Sheet Drawer, Optional furniture required., 2,000-Sheet High-Capacity Feeder, 500-Sheet Offset Stack, 500-Sheet Staple Finisher, 500-Sheet Staple Punch Finisher	5-Bin Mailbox, 550-Sheet Drawer, Optional furniture required., 2,000-Sheet High-Capacity Feeder, 500-Sheet Offset Stack, 500-Sheet Staple Finisher, 500-Sheet Staple Punch Finisher	5-Bin Mailbox, 550-Sheet Drawer, Optional furniture required., Banner Media Tray, 2,000-Sheet High-Capacity Feeder, 500-Sheet Offset Stack, 500-Sheet Staple Finisher, 500-Sheet Staple Punch Finisher	5-Bin Mailbox, Banner Media Tray, 500-Sheet Offset Stack, 500-Sheet Staple Finisher, 500-Sheet Staple Punch Finisher
Paper Input Capacity, Standard: Up to	650 pages 20 lb or 75 gsm bond	650 pages 20 lb or 75 gsm bond	1200 pages 20 lb or 75 gsm bond	2300 pages 20 lb or 75 gsm bond
Paper Input Capacity, Maximum: Up to	3200 pages 20 lb or 75 gsm bond	3200 pages 20 lb or 75 gsm bond	3200 pages 20 lb or 75 gsm bond	2300 pages 20 lb or 75 gsm bond
Media Types Supported	Card Stock, Dual Web Labels, Envelopes, Glossy Paper, Integrated Labels, Paper Labels, Plain Paper, Polyester Labels, Transparencies, Vinyl Labels, Refer to the Card Stock & Label Guide, Outdoor Media, Banner Paper			
General				
Function	Color Printing			
Product Warranty	1-Year Onsite Service, Next Business Day			
Product Certifications	www.lexmark.com			
Specified Operating Environment	Temperature: 16 to 32°C (60 to 90°F), Humidity: 8 to 80% Relative Humidity, Altitude: 0 - 3048 Meters (10,000 Feet)			
Size (in. - H x W x D)	20.3 x 22.3 x 20.2 in.	20.3 x 22.3 x 20.2 in.	25.5 x 22.3 x 20.2 in.	40.5 x 26.1 x 25.9 in.
Weight (lb.)	110 lb.	110 lb.	131 lb.	231 lb.
Furniture				
Caster Base	Optional, (Required for floor standing configuration)	Optional, (Required for floor standing configuration)	Optional, (Required for floor standing configuration)	(Included)
Spacer	Available	Available	Available	

Recommended Monthly Page Volume

«Recommended Monthly Page Volume» is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage.

Maximum Monthly Duty Cycle

«Maximum Monthly Duty Cycle» is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs.

Trademarks

Lexmark and Lexmark with the diamond design are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. All other trademarks are the property of their respective owners. ENERGY STAR® is a U.S. registered mark. Information in this document is subject to change without notice. PANTONE® is a registered trademark of Pantone, Inc. This product features Adobe® Flash® technology. For further information, visit <http://www.adobe.com/software/flash/about/>

Print Less. Save More.

www.lexmark.com



LEXMARK™