

Contractor Series 4 and 8 Ohms Weather-Resistant Horn Speakers

- SPC10** 6" Weather-Resistant Aluminum Horn - 8 Ohms
- SPC104** 6" Weather-Resistant Aluminum Horn - 4 Ohms
- SPC15** 8" Weather-Resistant Aluminum Horn - 8 Ohms
- SPC30** 15" Weather-Resistant Aluminum Horn - 8 Ohms

Features

- Weather-resistant, aluminum construction
- Includes mounting bracket
- Rubber bell protector
- 2 year warranty



Specifications	SPC10	SPC104	SPC15	SPC30
RMS Power	10W	10W	15W	40W
Max. Power.....	15W	15W	25W	75W
Termination Type	Wire strip	Wire strip	Wire strip	Wire strip
Sensitivity (1W/1M).....	105dB	105dB	110dB	120dB
Maximum SPL (Pmax/1m).....	108dB	108dB	115dB	111dB
Driver Impedance	8 Ohms	4 Ohms	8 Ohms	8 Ohms
Magnet.....	5.4 oz. ferrite	5.4 oz. ferrite	6.6 oz. ferrite	13.3 oz. ferrite
Frequency Response Range.....	250Hz ~ 15kHz	250Hz ~ 15kHz	200Hz ~ 15kHz	200Hz ~ 15kHz
Dispersion@100Hz	65° conical	65° conical	75° conical	90° conical
Speaker Dimensions	6" (Dia.) x 5.9" (D)	6" (Dia.) x 5.9" (D)	8" (Dia.) x 8" (D)	15" (Dia.) x 14" (D)
Weight	1.9 lbs.	1.9 lbs.	2.2 lbs.	4.9 lbs.
Material.....	Aluminum	Aluminum	Aluminum	Aluminum
Color.....	Grey	Grey	Grey	Grey

NDAA
COMPLIANT

*Products are in compliance with NDAA Section 889 Part B Guidelines

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 3/21/22