

Uncontrolled document as of May 18, 2006. Refer to website for up to date specifications.

CASES

1010

Micro Case



1010 Micro Case

- Totally watertight, crushproof
- Rubber liner for extra protection doubles as o-ring seal
- Pressure Equalization Valve – balances interior pressure, keeps water out
- Easy open latch
- Stainless steel hardware
- Lanyard
- Lifetime guarantee
- Available in clear with color liner or solid

1010 Micro Case Configurations

Cat. #	Description	Sug. Retail
1010	1010 Micro Case	\$12.95



Black



Yellow



Blue



Red

1010 Micro Case Specifications

Exterior Dimensions (L x W x D)		Interior Dimensions (L x W x D)	
5.43" x 4.06" x 2.12" (13.8 x 10.3 x 5.4 cm)		4.37" x 2.87" x 1.68" (11.1 x 7.3 x 4.3 cm)	
Lid Depth	Bottom Depth	Total Depth	
0.69" (1.8 cm)	0.94" (2.4 cm)	1.63" (4.1 cm)	
Weight w/Foam	Weight w/o Foam	Buoyancy Max.	
0.41 lbs. (0.19 kg)	0.4 lbs. (0.18 kg)	0.51 lbs. (0.23 kg)	
Range Temperature			
-10 / 199.4° F (-23 / 93° C)			

1010 Micro Case Certificates

- IP67

1010 Micro Case Accessories

Cat. #	Description	Sug. Retail
1011	Replacement Case Liner	\$1.80
1012	Pick 'N' Pluck™ Foam Insert	\$4.50

Pelican™ Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
e-mail: sales@pelican.com • www.pelican.com