
Rack B B B B B



For the small network room **and** enterprise data centers

The Open Frame Server Rack is designed to provide users with a customizable solution engineered to meet a diverse set of rack mounting needs.

This EIA server rack uses universal square holes and is compatible with 19" equipment developed by the leading OEMs.

The Open Frame Rack is perfect for both small offices and large data centers as it is available in sizes from 5U to 70U and depths of 20", 24", and 28" making this the ideal mount racking solution.

Rack 111 Catalog



Technical Specifications

Rack Units

- 5U, 16U, 24U, 30U, 36U, 44U, ٠ 50U, 55U, 58U
- Hole Type
- EIA 3/8" (9.5 mm) square hole . Rack Mounting Depth
- 28.875" (733 mm) 24"(610 mm) 20" depth (508 mm)

Weight Capacity

- 3000 lbs (1360 kgs) without casters 1200 lbs (544 kgs) with casters
- Included Hardware
- (40) 12-24 cage nuts
- (4) Masonry anchors
- Masonry drill bit •

Options

- Cable management .
- Caster kit
- Rack tops
- Side panels
- **Blanking** Panels

Rack Outside Dimensions

Width = 24" (609 mm) Depth = 28.875", 24" or 20"

Height

5U = 15'' (381 mm)16U = 34" (863 mm) 24U = 48" (1219 mm) 30U = 58.5" (1485 mm) 36U = 69" (1752 mm) 44U = 83" (2108 mm) 50U = 93.5" (2375 mm) 55U = 103" (2616 mm) 58U = 108" (2743 mm) 70U = 123" (3124 mm)

Certification

UL Certified •

| P/N | DESCRIPTION |
|----------|-------------------------------------|
| 111-2257 | 16U Open Frame Rack - 28 7/8" Depth |
| | Depth |
| 111-1779 | 20" Depth Kit, Open Frame Rack |
| 111-1778 | 24" Depth Kit, Open Frame Rack |
| 111-1725 | 28 7/8" Depth Kit, Open Frame Rack |
| | Height |
| 111-4620 | 5U, Height Kit, Open Frame Rack |
| 111-2258 | 16U, Height Kit, Open Frame Rack |
| 111-1726 | 24U, Height Kit, Open Frame Rack |
| 111-1727 | 30U, Height Kit, Open Frame Rack |
| 111-1728 | 36U, Height Kit, Open Frame Rack |
| 111-1729 | 44U, Height Kit, Open Frame Rack |
| 111-1730 | 50U, Height Kit, Open Frame Rack |
| 111-4596 | 55U Height Kit, Open Frame Rack |
| 111-4597 | 58U Height Kit, Open Frame Rack |
| | |
| 111-5215 | 70U Open Frame Rack |
| | |
| 100-1319 | Baying Kit, Open Frame Rack |

Don't Leave Your Cables Hanging

Vertical Cable Bars

The Vertical Cable Bar is available in various sizes to meet the needs of customers in small offices or large data centers.

Features & Benefits

- Keep cables organized
- Add multiple cable bars
- Supports powers strips
- Provides unrestricted airflow
- Multiple wire tie points




Cable Management Options

| 5″ CM |
|--|
| • 137-2412 • 137-1707 |
| 137-0318 137-0317 137-0316 |
| • 137-0315 • 137-0314 |
| |
| |
| |
| |

5" CMA

58U, 5" Vertical Cable Organizer • 137-2412 55U, 5" Vertical Cable Organizer 50U, 5" Vertical Cable Organizer • 137-0318 • 137-0317 44U, 5" Vertical Cable Organizer •137-0316 36U, 5" Vertical Cable Organizer • 137-0315 30U, 5" Vertical Cable Organizer • 137-0314 24U, 5" Vertical Cable Organizer



11" CMA

•137-4634 58U, 11" Vertical Cable Organizer • 137-4651 55U, 11" Vertical Cable Organizer • 137-4650 50U, 11" Vertical Cable Organizer • 137-4196 44U, 11" Vertical Cable Organizer • 137-5940 70U, 11" Vertical Cable Organizer

Additional Products

Rack Tops

| • 113-1834 | 28″ Depth Rack Top without cable pass-through (black) |
|------------|--|
| • 113-1832 | 28″ Depth Rack Top with cable pass-through (black) |
| • 113-3604 | 24" Depth Rack Top without cable pass-through (black) |
| •113-3065 | 20″ Depth Rack Top with cable pass-through (black) |

Options include:



- Solid tops

- Tops with cable pass-throughs

Features & Benefits

- Helps control rack air flow
- Grommet edging around holes
- Solid steel construction
- Supports cabling, trays, ladders
- Prevents debris from falling into the rack


Caster Kits

- 111-1731 Caster Kit, Open Frame Rack
- 131-4777 Caster Kit with leveling feet, Open Frame Rack



FEATURES & BENEFITS

- Front swivel casters
- Rear, non-swivel casters
- Non-marring wheels
- Wheels do not lock
- 1200 lb weight capacity



"When we completed a 20,000 sf data center expansion we needed about 20,000 server racks to complete the project. RackSolutions had the best product, the best customer service and as it turns out the best price too." -Hivelocity.net

Vertical Power Strip

- PSV-F8-15A-Q • PSV-F16-15A-R
- PSV-F24-15A-S
 PSV-F8-20A-T
 PSV-F16-20A-U
- 15A, 24 Outlets, 15ft Cord (44U+ racks) 20A, 8 Outlets, 15ft Cord (24U+ racks)

15A, 8 Outlets, 15ft Cord (24U+ racks) 15A, 16 Outlets, 15ft Cord (30U+ racks)

- 20A, 16 Outlets, 15ft Cord (30U+ racks) 20A, 24 Outlets, 15ft Cord (44U+ racks)
- PSV-F24-20A-V 20A, 24 Outlets, 15ft Cord (44U+ racks)
 Rack-111-PSMOUNT Power Strip Mounting Brackets for Rack Model 111

Features & Benefits

- NEMA 5-15 plugs and receptacles
- 15A and 20A model options
- 8, 16, and 24 outlets
- CSA certified and UL recognized



Air Flow Control

Side Panels

RackSolutions' tool-less Side Panels come in a variety of sizes. Each side is divided into 2 or 3 sections (depending on rack height) to make installation easy.

- 102-2453 58U, Side Panels (sold per side) BTO
- 102-1709 55U, Side Panels (sold per side) BTO 50U, Side Panels (sold per side) • 102-1777
- 102-1776 44U, Side Panels (sold per side)
- 102-1775 36U, Side Panels (sold per side)
- 102-1774 30U, Side Panels (sold per side)
- 102-1773 24U, Side Panels (sold per side)
- 102-2260 16U, Side Panels (sold per side)

Features & Benefits


- Helps control rack air flow
- Professional appearance
- Perfect for end row racks
- Solid steel construction
- Black, powder coated finish

Blanking Panels

Blanking Panels work best to control the air flow through the server racks. Without the use of blanking panels, the hot exhaust air from the servers can be recirculated through the cabinet and significantly reduce the cooling efficiency of the system.

Features & Benefits

- Controls rack air flow
- Professional appearance
- Compatible with all EIA standard 19" racks and cabinets



Blanking Panel Options

Standard

| • 102-1822 | 1U, Basic Blanking Panel |
|------------|--------------------------|
| • 102-1823 | 2U, Basic Blanking Panel |
| • 102-1824 | 3U, Basic Blanking Panel |
| • 102-1825 | 4U, Basic Blanking Panel |
| •102-1826 | 5U, Basic Blanking Panel |
| •102-1827 | 6U, Basic Blanking Panel |
| •102-1828 | 7U, Basic Blanking Panel |
| • 102-1829 | 8U, Basic Blanking Panel |



Tool-less

• 102

| • 102-1474 | 1U, Tool-less Blanking Panel |
|------------|------------------------------|
| • 102-1475 | 2U, Tool-less Blanking Panel |
| • 102-1476 | 3U, Tool-less Blanking Panel |
| • 102-1477 | 4U, Tool-less Blanking Panel |
| • 102-1478 | 5U, Tool-less Blanking Panel |
| • 102-1479 | 6U, Tool-less Blanking Panel |
| • 102-1481 | 8U, Tool-less Blanking Panel |



Perforated

• 102-1881

• 102-1882

• 102-1883 • 102-1886

• 102-1888

| 1U, Vented Blanking Panel with Stability Flanges |
|--|
| 2U, Vented Blanking Panel with Stability Flanges |
| 3U, Vented Blanking Panel with Stability Flanges |
| 6U, Vented Blanking Panel with Stability Flanges |
| 8U. Vented Blanking Panel with Stability Flanges |



Manage Your Rack's Airflow

Air Dam

The Air Dam from RackSolutions helps direct the air toward the rack equipment, instead of at the ceiling. Choose between a 5" or 10" air dam that runs the length of the Rack 111. The adjustable sizes of the side air dams allow this option to work with Rack 111's in heights from 44U-58U.

- 123-2101 5" Top Air Dam for Open Frame Rack
 123-2267 10" Top Air Dam for Open Frame Rack
 123-4170 Adjustable Side Air Dam
- 123-4266 Air Dam Floor Skirt Kit • 123-4265 Air Dam, Adapter,
- 123-4265 Air Dam, Adapter, 5" to 10", Top

Features & Benefits

- Top & Side Air Dams sold separately
- Choose from 5" or 10" sizes
- Quick and easy installation
- No measurable, by-pass air
- High density server installations



RackSolutions is a market leader in IT infrastructure products.

Founded in 1999, RackSolutions pioneered rack mounting solutions for servers in the telecommunications industry. Today our product lines consist of high quality racks and server cabinets engineered for data centers and IT offices. We also offer a complete line of server rail kits, shelves and brackets designed and built to make mounting IT hardware simple.

RackSolutions' headquarters is located in Greenville, Texas. We manufacture our products at our own state-of-theart facilities in Texas. Additionally, RackSolutions operates from multiple sites globally including offices and warehouses in Canada, Great Britain, and Luxembourg.

Hundreds of our products are available through a global network of distributors in America, Asia, Europe and the Middle East. This allows for immediate shipment of our products to meet tight project schedules and to keep shipping costs low.

At RackSolutions, we understand that commercial products do not always support every company's unique requirements. If our standard products do not meet your specific project needs, the RackSolutions' engineering team will work with you directly to develop and manufacture an innovative product solution.





Since all our engineering and design is done at our office adjacent to our primary manufacturing facility, there is a reduction in turnaround time and overhead cost. Because of this, we can offer custom fabrication at "off the shelf" pricing.

Whether it's a small project or a high volume program, RackSolutions will deliver a quality and cost effective product at a reasonable price.

RackSolutions.com Toll Free

888.903.RACK(7225)

Email info@RackSolutions.com





"RackSolutions@" and "RackSolutions.com" are registered trademarks of RackSolutions, Inc. @Copyright 2019. Server Racks, Rack Mount Problem Solvers. All Rights Reserved. All other marks of others are property of their respective owners

RackSolutions.com