

HSM® Classic

411.2 OMDD

Powerfully destroys CD/DVDs



- NSA Tested - meets NSA requirements for OMDD (Optical Media Destruction Device)
- Included in the NSA/CSS Evaluated Product List (EPL 04-02)
- Ensures performances adheres to strict capability standards
- High speed performer - up to 10x more destruction capacity than most competitive models
- Retains on-site control of media ensuring higher security measures are followed
- Specially hardened 100% solid steel cutting rollers
- Fan cooled 2.8 horsepower motor
- Infeed slot for CD/DVDs
- Safety element prevents unintentional entry and serves as a splinter shield
- Keypad control for constant operation and reverse
- Photoelectric cell for automatic start/stop
- Mobile on castors
- Convenient automatic reverse in the event of material jam
- Stops automatically when waste bag is full or door is open
- Anti-Jam technology designed to easily and quickly reverse in the event machine is overloaded
- Uses a 58 gallon capacity shred bag; Part #HSM2117



HSM part#	HSM1570
Cutting type	Cross cut
Cutting size	0.086" x 0.157"
Security level DIN 32757-1	6
Security level DIN 66399	O-5 / T-6 / E-5
Cutting capacity per run in pieces	2500 pcs / hr
Cutting Speed	24 ft / min
Throat opening	16"
Motor at maximum	2100W
Motor power (horsepower)	2.82
Voltage	115 V / 60Hz
Dimensions (H x W x D)	37 4/5" x 23 2/5" x 18 1/2"
Weight	181 lbs
Shred-bin volume	38.5 gal
Cutting capabilities	

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
 419 Boot Road
 Downingtown, PA 19335
 www.hsmofamerica.com
 Customer Service: 800.613.2110

Great Products, Great People.

HSM®