

SmartRack Wall-Mount Roof Fan Kit - 2-120V high-performance fans; 210 CFM; 5-15P plug

MODEL NUMBER: SRFANWM



Highlights

- Wall-Mount Roof Fan Kit - 120V
- Features (2) 120V high-performance fans, 3-ft. (0.91 m) cord
- 50 dB sound rating

Package Includes

- (2) 120V high-performance fans with 3-ft. (0.91 m) power cord
- (2) Fan guards
- Mounting hardware
- Owner's manual

Increase airflow in wall-mount rack enclosures. The SRFANWM is ideal for expelling heat through a roof mounted fan system.

Features

- (2) 120V High-Performance Fans (210 CFM total)
- 50 dB sound rating
- 3-ft. (0.91 m) AC input cord with 5-15P input plug

Specifications

OVERVIEW	
UPC Code	037332166616
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Nominal Input Voltage Description	120V 50/60 Hz
Input Plug Features	NEMA 5-15P
Input Cord Length (ft.)	3
Input Cord Length (m)	0.91
COOLING	
Cooling Type	Passive



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Shipping Dimensions (hwd / cm)	7.87 x 19.81 x 29.62
Shipping Dimensions (hwd / in.)	3.10 x 7.80 x 11.66
Shipping Weight (kg)	2.30
Shipping Weight (lbs.)	5.08
Unit Dimensions (hwd / cm)	Per Fan 13.21 x 13.21 x 4.1
Unit Dimensions (hwd / in.)	5.20 x 5.20 x 1.61
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>