

3 ft DisplayPort™ to Mini DisplayPort 1.2 Video Cable Adapter M/F - DisplayPort 4k

StarTech ID: DP2MDPMF3



The DP2MDPMF3 3ft DisplayPort™ to Mini DisplayPort 1.2 Cable Adapter turns a Mini DP male connector into a regular DisplayPort male connector, making it easy to connect a Mini DisplayPort-equipped monitor to a laptop that only provides a standard DisplayPort output (e.g. Toshiba® etc.).

The DP to Mini DP cable supports high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The DP2MDPMF3 is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Applications

- Allows mini DisplayPort monitors, such as Apple Cinema Displays to be connected to computers equipped with standard DisplayPort connections

Features

- High-resolution support of up to 4k x 2k
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6 Gbps
- Designed and manufactured to DisplayPort 1.2 standards
- Backward compatible with DisplayPort 1.1
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Molded Mini DisplayPort connectors with strain relief

Technical Specifications

Warranty	Lifetime
Number of Conductors	20
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Connector A	1 - DisplayPort (20 pin) Male
Connector B	1 - Mini-DisplayPort (20 pin) Female
Color	Black
Wire Gauge	32 AWG
Cable Length	3 ft [0.9 m]
Product Length	3 ft [0.9 m]
Product Width	0.1 ft [0 m]
Product Height	0 ft [0 m]
Product Weight	0.1 lb [0 kg]
Operating Temperature	0°C to 35°C (32°F to 95°F)
Storage Temperature	0°C to 70°C (32°F to 158°F)
Humidity	0~80% RH
Package Quantity	1
Shipping (Package) Weight	0.1 lb [0.1 kg]
Included in Package	1 - 3 ft DisplayPort™ to Mini DisplayPort Video Cable Adapter - M/F

Certifications, Reports and Compatibility

