

4U 19in Secure Horizontal Wall Mountable Server Rack - 2 Fans Included

StarTech ID: RK419WALVSGB



The RK419WALVSGB 4U 19-inch Secure Horizontal Wall-Mountable Server Rack is a lockable, solid steel storage rack that provides a robust solution for wall mounting telecom, network or server equipment, and includes two 120mm fans, for improved airflow. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This 4U rack can be mounted to a wall in a server room, office, or above a doorway in rooms lacking the space for a full-size rack, to expand your workspace and keep your equipment protected from unauthorized access. The bracket mounting holes (used to mount to a wall or desk) are positioned at 16-inches apart, matching standard stud measurements for easy installation.

Constructed to EIA-RS310 standards, the wallmount server rack allows equipment to be mounted horizontally, and offers a hinged lockable front cover as well as a lockable body. Alternatively, non-rackmount equipment can be mounted vertically with the included bottom cover, using the rack as a wall case.

Backed by a StarTech.com Lifetime warranty.

Applications

- Securely mount servers and telecommunication equipment flush against the wall
- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or retail supercenter
- Install a large server anywhere in an office without a full server room, while protecting against unauthorized access
- Ideal for small and medium businesses requiring small, secure rack solutions dispersed throughout the organization

Features

- Includes optional 4U steel plate which acts as a shelf, allowing the rack to be used as a wall case for any non-rackmount equipment
- Hinged, lockable front cover
- TAA compliant for GSA Schedule purchases
- Both the top cover and the rack body are lockable separately for varying security levels
- 2 x 120mm fans included
- Wall mounting holes are 16in center to center, for greater stability and mounting to standard wall studs
- Compatible with most 19in wide rack-mountable equipment
- Solid steel construction
- Constructed to meet the EIA-RS310 19in rack standards

Technical Specifications

Warranty	Lifetime
Fan(s)	Yes
Fans	2 - 120 mm
Frame Type	Enclosed Cabinet
Front Door Type	Solid Steel
Industry Standards	EIA RS310-D
Key Lock	Yes
Rack Type	2-Post
U Height	4U
Wallmountable	Yes
Air Flow Rate	92/106 CFM
Noise Level	42/46 dBA
Weight Capacity	68 kg [150.3 lb]
Input Voltage	110 ~ 240 AC
Power Source	International Power Cords
Color	Black
External Depth	725 mm [28.5 in]
External Height	224 mm [8.8 in]
External Width	643 mm [25.3 in]
Internal Depth	585.2 mm [23 in]
Internal Height	177.8 mm [7 in]
Internal Width	485 mm [19.1 in]
Maximum Mounting Depth	520.7 mm [20.5 in]
Product Weight	20.1 kg [44.5 lb]
Flat Pack	No
Shipping (Package) Weight	22 kg [48.6 lb]
Included in Package	1 - RK419WALVS 4U Wallmount rack
Included in Package	1 - Set of Keys
Included in Package	1 - UK to EU plug converter
Included in Package	24 - #10-32 Panel Screws

Certifications, Reports and Compatibility

