


Epson AcuLaser C3900N series

DATASHEET



Get fast, high-quality colour printing with the Epson AcuLaser C3900N series. Offering the speed and flexibility to meet the demands of medium workgroups, it prints up to 30 colour or mono A4 pages per minute.

With a low total cost of ownership, the series represents excellent value for money and your business can optimise its running costs with high yield toners and double-pack black toner cartridges.

Big print jobs are no problem for this high-performance laser series, which has optional automatic duplex and two paper trays as standard with an optional additional 500-sheet tray. As your business grows, the AcuLaser C3900N series keeps pace with its expandable RAM and HDD.

Compact and easy to use, with a large LCD screen, the AcuLaser C3900N series fits effortlessly into your office. It integrates into your IT environment with PLC6, PS3, XPS and PDF1.7 emulations, advanced IPv6 protocols and Gigabit Ethernet support. Advanced IPsec/SSL support improves the security of sensitive materials.

KEY FEATURES

- Fast colour and mono printing at 30ppm
- Expandable paper capacity up to 850 sheets
- Compact design
- Large LCD screen
- Seamless IT integration



An optional additional 500-sheet tray increases paper capacity to 850 sheets.

EPSON®
EXCEED YOUR VISION

PRODUCT SPECIFICATIONS

TECHNOLOGY	
Print technology	Laser
Print resolution	Up to 600 x 600dpi
PRINT	
Print speed	Up to 30ppm (colour and monochrome A4)
First page out	12.9 seconds
Maximum monthly volume	Up to 120,000 pages per month
Warm up time	39 seconds
CONNECTIVITY	
Printer interface	Gigabit Ethernet, USB 2.0 compliant, USB 2.0 compliant host
Network printing protocols	TCP/IP: IPP 1.1, LPD, FTP, WSD, Port9100 AppleTalk: PAP Netware: Print Server (NDS, Bindery)
Network management protocols	TCP/IP: TCP/IPv4, TCP/IPv6, IP/Sec, DHCP, SNMP v1/v2c/v3, BootP, ARP, HTTP v1.1, HTTPS, SMTP v1, SNTP, SLP v2, DDNS, WSD, AutoIP, Ping AppleTalk: EtherTalk Netware: IPX/SPX
PAPER HANDLING	
Standard paper input	Up to 350 sheets
Paper size	A4, A5, A6, B5, B6, F4, EXE, DL, LT, GLT, LGL, GLG, HLT, 16K, UK Quarto, Label, Envelope (C6, ISO-B5, Com-10), SP Folio, Foolscap, Postcard, custom: 92 x 148mm to 216 x 356mm
Duplex	Standard on DN model
Paper weight	60–210g/m ²
Paper output	Up to 200 sheets (face down)
Optional paper handling	Optional 500-sheet paper tray (maximum 1)
Maximum paper input	850 sheets (100-sheet MP tray + 250-sheet paper tray + 1 optional 500-sheet paper tray)
POWER REQUIREMENTS	
Power consumption	Max: 1200W, Continuous printing: 460W, Ready: 166W, Sleep: 34W, Power Off: 0W
Voltage	AC 220–240V ±10%
Current	±3Hz / 4.6A
Frequency range	50Hz / 60Hz
DIMENSIONS (W x D x H)	419 x 520 x 330mm (without manual feed tray)
WEIGHT (without consumables)	N model: 21.5kg, DN model: 22.3kg
GENERAL	
Sound power	Printing mode: 7.0B, Standby mode: 4.85B
Sound pressure	Printing mode: 54dB (A), Standby mode: 39dB (A)
Operating temperature	Operation mode: 10–30°C, Storage: 0–35°C
Operating humidity	Operation mode: 15–85%RH, Storage: 30–85%RH
Windows support	Windows 7, Vista (32/64bit), XP (32/64bit), Windows 2000, Server 2003 (32/64bit), Server 2008 (32/64bit), Server 2008R2 (64bit)
Mac support	Mac OSX 10.3.9 or later
Operating systems	For compatibility details relating to Linux, Unix, Novell, SAP, etc. please refer to http://www.business-solutions.epson.co.uk/compatible.htm
OTHER FEATURES	
Energy Star	On DN model only
Processor	800MHz
Memory	Standard: 256MB. Maximum: 768MB
Printer control language emulations	PCL6, PCL5e, PCL5c, PS3, XPS and PDF 1.7 emulations
Resident typefaces	Scalable: 93 PCL5c, 93 PCL6, 137 PS3, Bitmap: 1 PCL5c, 1 PCL6
LCD	Yes
WARRANTY	
Standard warranty	One-year on-site warranty
Optional warranty	Three-year on-site extended warranty

PRODUCT MODEL ORDER CODES

- **AcuLaser C3900N** XXXXXXXXXXXXXXX
- **AcuLaser C3900DN** XXXXXXXXXXXXXXX
(with duplex)
- **AcuLaser C3900DTN** XXXXXXXXXXXXXXX
(with duplex and additional paper tray)

WHAT'S IN THE BOX

- Printer
- Power cable
- Software CD
- Instruction manuals
- Warranty sheet

SUPPLIES

- **Black High Capacity Toner Cartridge** (6,000 pages*) C13S050593
- **Double-pack Black High Capacity Toner Cartridge** (2 x 6,000 pages*) C13S050594
- **Cyan High Capacity Toner Cartridge** (6,000 pages*) C13S050592
- **Magenta High Capacity Toner Cartridge** (6,000 pages*) C13S050591
- **Yellow High Capacity Toner Cartridge** (6,000 pages*) C13S050590
- **Black Photoconductor Unit** (30,000 pages**) C13S051204
- **Cyan Photoconductor Unit** (30,000 pages**) C13S051203
- **Magenta Photoconductor Unit** (30,000 pages**) C13S051202
- **Yellow Photoconductor Unit** (30,000 pages**) C13S051201
- **Fuser Unit** (100,000 pages**) C13S053041
- **Waste Toner Bottle** (9,000 CMY, 36,000 K pages**) C13S050595
- **Initial Toner Cartridge** (2,000 pages*)

* According to ISO/IEC 19798 yield measurements.

** Yield may vary depending on printing variables and conditions including toner and page coverage, continuous or intermittent.

OPTIONAL ACCESSORIES

- **500-sheet paper tray** C12C802651
- **Hard Disk Drive** C12C824511



EPSON
COVERPLUS

Better Products
for a Better Future

For further information please contact your local Epson office or visit www.epson-europe.com

Austria 0810/20 01 13 (0,07 €/Min.) **Belgium** 070/350120 (0,1735 €/min.) **Czech** 800/142 052 **Denmark** 44 50 85 85 **Finland** 0201 552 091
France 09 75 04 04 (Cost of local call, operator charges may apply) **Germany** 01805/23 41 10 (0,14 €/Min. aus dem dt. Festnetz, Mobilfunkpreise abweichend. Ab 1.3.2010 Mobilfunkpreis max. 0,42 €/Min.) **Greece** 210-8099499 **Hungary** 06800 147 83 **Ireland** 01 436 7742 **Italy** 02-660321 10 (0,12 €/min.) **Luxembourg** 900/43010 (0,24 €/min.) **Middle East** +971 8818934 **Netherlands** 0900-5050808 (0,05 €/oproep + 0,15 €/min.)
Norway +47 67 11 37 00 **Poland** 0-800 4911299 (0,16 zł/min.) **Portugal** 707 222 111 **Russia** (095) 777-03-55 **Slovakia** 0850 111 429
South Africa (+2711) 465-9621 **Spain** 93 582 15 00 **Sweden** 0771-400135 (Mobilansamtal - 0,99 kr/min, Lokala samtal - 0,30 kr/min, Utlandssamtal - 0,89 kr/min)
Switzerland 0848 448820 (4-8 cent./min.) **Turkey** (0212) 3360303 **United Kingdom** 0871 222 6702

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.