

15m CAT6 Ethernet Cable - Black CAT 6 Gigabit Ethernet Wire -650MHz 100W PoE RJ45 UTP Network/Patch Cord Snagless w/Strain Relief Fluke Tested/Wiring is UL Certified/TIA

Product ID: N6PATC15MBK



The N6PATC15MBK Cat 6 Patch Cable (15m) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable black PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat 6 Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This Cat 6 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifications, Reports and Compatibility

Applications

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet
- Extend the reach of your Gigabit network devices by 15m (49.2ft)

Features

- High quality 24 AWG copper wire
- ETL Verified
- HIGH PERFORMANCE CAT6 ETHERNET CABLE: 100% copper for error-free Multi Gigabit 1/2.5/5Gbps connections; 10Gbps up to 50m; Fluke patch cord tested to comply w/ANSI/TIA-568-2.D Category 6 & ETL Verified
- POE SUPPORT: 24 AWG stranded copper conductors & UL Rated Wiring (E132276-A) supports up to 100W for PoE devices like VOIP phone & security systems; IEEE 802.3bt & DTE power compliance reduces cable heating
- QUALITY CONSTRUCTION: ETL & UL certified wire; 50-micron gold-plated connectors prevent rust/corrosion to avoid costly network downtime; High quality PVC jacket resists bending or fraying damage
- EASY INSTALLATION: Snagless patch cord for easy installation & flexible disconnection in wiring conduits; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- SPECS: Length: 15m (50ft) Color: Black 650 MHz Rated Structure: 4 Pair UTP RJ45 Jacket: PVC Wire Gauge: 24 AWG Copper Wiring: ANSI/T568B ETL Verified Warranty: Lifetime

Prominence

| Warranty | Lifetime |
|-------------------------------|--|
| Description CDW 75 - 1st Line | StarTech.com CAT6 Ethernet Cable 15m Black 650MHz 100W Snagless Patch Cord |

Hardware

| | |
|-----------------------|-----------------------------|
| Number of Conductors | 4 pair UTP |
| Connector Plating | Gold |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Fire Rating | CMG Rated (General Purpose) |
| Cable Type | Snagless |
| Wiring Standard | TIA/EIA-568-B.1-2001 T568B |



Performance

| | |
|--------------|----------------|
| Cable Rating | CAT6 - 650 MHz |
|--------------|----------------|

Connector(s)

| | |
|-------------|-------|
| Connector A | RJ-45 |
|-------------|-------|

| | |
|-------------|-------|
| Connector B | RJ-45 |
|-------------|-------|

Physical Characteristics

| | |
|-------|-------|
| Color | Black |
|-------|-------|

| | |
|------------|--------|
| Wire Gauge | 24 AWG |
|------------|--------|

| | |
|----------------|-----------------|
| Conductor Type | Stranded Copper |
|----------------|-----------------|

| | |
|--------------|----------------|
| Cable Length | 49.2 ft [15 m] |
|--------------|----------------|

| | |
|----------------|----------------|
| Product Length | 49.2 ft [15 m] |
|----------------|----------------|

| | |
|-------------------|-----------------|
| Weight of Product | 20.8 oz [588 g] |
|-------------------|-----------------|

Packaging Information

| | |
|------------------|---|
| Package Quantity | 1 |
|------------------|---|

| | |
|----------------|-----------------|
| Package Length | 13.0 in [33 cm] |
|----------------|-----------------|

| | |
|---------------|-------------------|
| Package Width | 10.0 in [25.5 cm] |
|---------------|-------------------|

| | |
|----------------|----------------|
| Package Height | 2.0 in [52 mm] |
|----------------|----------------|

| | |
|---------------------------|-----------------|
| Shipping (Package) Weight | 21.3 oz [604 g] |
|---------------------------|-----------------|

What's in the Box

| | |
|---------------------|---|
| Included in Package | 15 m Black Snagless Cat6 UTP Patch Cable - ETL Verified |
|---------------------|---|

****Product appearance and specifications are subject to change without notice.***

