

2 Port Industrial Wall Mountable USB to Serial Adapter Hub with DIN Rail Clips

Product ID: ICUSB2322I



The ICUSB2322I 2-Port Industrial USB to Serial Hub with DIN Rail Clips converts a single USB port into two RS232 serial ports, enabling you to connect to, monitor and control your serial devices.

Featuring rugged metal construction, with sturdy wall-mounting brackets and top-hat DIN Rail clips (included), this USB to Serial Hub provides versatile mounting options and a robust solution for both harsh industrial environments and simple desktop installations.

This USB powered adapter also retains assigned serial COM port values once connected, allowing the same values to be automatically reassigned to the ports provided by the adapter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect a satellite receiver, serial modem, or PDA with serial sync
- Connect and program LED and Digital signage boards with serial communication ports

Features

- 2-port USB to RS232 serial adapter
- Rugged metal construction
- Wall-mountable, with included DIN Rail clips
- COM retention: COM Port assignments maintained across reboot
- Baud Rate up to 921.6 Kbps
- Powered by an available USB port - no external power adapter required

Hardware	Warranty	2 Years
	Bus Type	USB 2.0
	Chipset ID	FTDI - FT232RL
	Interface	Serial
	Port Style	External Hub
	Ports	2
Performance	Data Bits	7, 8
	FIFO	256 Bytes
	Max Baud Rate	921.6 Kbps
	Parity	Odd, Even, Mark, Space, None
	Serial Protocol	RS-232
	Stop Bits	1, 2
Connector(s)	External Ports	1 - USB B (4 pin) Female 2 - DB-9 (9 pin, D-Sub) Male
	OS Compatibility	Windows® CE (4.2, 5.0, 6.0), XP Embedded, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2012 R2, 2016 Mac OS® 10.6 to 10.14 Linux 2.4.x to 4.11.x <i>LTS Versions only</i>
Indicators	LED Indicators	2 - Each, Tx/Rx Activity indicators
Power	Power Source	USB-Powered
Environmental	Humidity	5~95% RH
	Operating Temperature	0°C to 55°C (32°F to 131°F)
	Storage Temperature	-20°C to 85°C (-4°F to 185°F)
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Color	Black
	Enclosure Type	Steel
	Product Height	0.9 in [2.4 cm]
	Product Length	4.1 in [10.4 cm]
	Product Width	2.6 in [66 mm]
	Weight of Product	5.7 oz [162 g]
Packaging Information	Package Height	1.6 in [41 mm]

	Package Length	8.4 in [21.4 cm]
	Package Width	5.7 in [14.5 cm]
	Shipping (Package) Weight	0.8 lb [0.4 kg]
What's in the Box	Included in Package	1 - USB to RS-232 Serial Adapter 1 - DIN rail kit 1 - 6 ft USB A to B cable 1 - Driver CD 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.