Canon

FAXPHONE L100

Laser Fax-based Multifunction Printer

(shown with tilted control panel)

- 33.6 Kbps **Super G3** fax[1]
- Up to **512 sheets of memory capacity**[2]
- **30 one-touch speed dials** and 100 coded dials for a comprehensive address book
- Telephone **handset included** as standard
- **Quick first print** arrives in just 8 seconds
- **Unique design** a fit for any home or small office
- Low energy consumption uses just **1.4W in Energy Saver mode**
- **Single Cartridge System** for easy supplies replenishment

Advanced Desktop Laser Performance

The FAXPHONE L100 combines the performance of a laser fax machine, laser printer and digital copier together for your small office or personal desktop. Incorporating the latest fax capabilities, a 19-page per minute laser print engine and a brand new copier function, this stylishly redesigned machine functions in the place of three devices.

With features such as a 30-sheet Automatic Document Feeder, 130 speed dials, Super G3 fax technology and a large 512-sheet fax memory, the FAXPHONE L100 surpasses single function fax machines.

Printed faxes and documents will both have the same results - quality laser output. The FAXPHONE L100 is the smart choice for desktop laser fax, print and copy performance.

| FAX 33.6 kbps | 19 Black ppm | QUICK 1st PRINT | 30 Speed Dials With Handset Included | 30 Sheets ADF | Memory Up To 512 Pages | COST & ENERGY EFFICIENT |

Canon

FAXPHONE L100

Technical Information

FAX SPECIFICATIONS

Modem Speed
33.6 Kbps (Super G3)[1]

Fax Resolution
Up to 200 x 400 dpi (super fine)

Transmission Time
MMR (approx 3.0 seconds)

Memory Capacity
Up to 512 sheets[2]; 5 minute backup

Speed Dialing
30 one-touch speed dials; 100 coded dials

Group Dialing
129 destinations

Sequential Broadcasting
140 destinations

PC Fax
Yes (TX only)

Fax Features
Dual Access, Remote RX, Distinctive Ring Pattern Detection, Error Correction Mode, Auto Redial, Manual Fax Forwarding, Activity Result & Activity Management Reports

Telephone Handset
Included

PRINTER SPECIFICATIONS

Print Speed
Up to 19 ppm (letter)

First Print Time
Approx. 8 seconds

Printer Language
UFR II LT (Host-based)

Print Resolution
Up to 600 x 400 dpi
(1200 x 600 dpi quality)

Print Size
5.5" x 5" to 8.5" x 14"

Print Memory
64MB (shared)

Print Modes
Watermark, Page Composer, Toner Saver

COPIER SPECIFICATIONS

Copy Speed
Up to 12 cpm (letter)

First Copy Time
Approx. 22 seconds[3]

Copy Resolution
Up to 600 x 600 dpi

Halftones
256 levels

Maximum # of Copies
99 copies

Zoom
50% - 200% in 1% increments

Copy Size
5.5" x 5" to 8.5" x 14"

Copy Features
Density Adjustment, Toner Saver Mode

PAPER HANDLING SPECIFICATIONS

Standard Paper Source(s)
150-sheet cassette[4]

Document Feeder
30-sheet Simplex[4]

Paper Output
Approx. 100 sheets (face down)

Paper Weight
16 to 43 lb. bond

Media Sizes
Letter, Legal, Statement, Executive, A4, A5, B5

Media Types
Plain Paper, Heavy Paper, Recycled Paper, Transparency, Label, Envelope

Envelope Capacity
10 envelopes

CONNECTIVITY & SOFTWARE SPECIFICATIONS

Standard Interface(s)
USB Device 2.0 Hi-Speed[5]

Operating Systems
Windows® 7, Windows Vista®, Windows XP/2000, Mac® OS X 10.4.9 & up, Linux[6] (print only)

Cable Included
Power Cord, Phone Cable (USB not included)

Drivers available for download from www.usa.canon.com

ENVIRONMENTAL SPECIFICATIONS

Power Consumption
During Operation: Approx. 410W
Standby: Approx. 10W
Energy Saver: Approx. 1.4W

Typical Energy Consumption (TEC)
0.6 kWh

Noise Level
During operation: 6.5 B or less (sound power)
53 dB (sound pressure)
During standby: 4.3 B or less (sound power)
Inaudible (sound pressure)

General Specifications

CPU
Canon Custom Processor (133 MHz)

Dimensions
14.7" (W) x 12.0" (D) x 12.0" (H)

Unit Weight (without/with cartridge)
18.1 lbs./19.5 lbs.

Package Weight
Approx. 25.4 lbs.

Warranty
1 year limited exchange/carry-in warranty[7] (Extended warranty available)

Cartridge 128
Yields approximately 2,100 pages based on ISO/IEC Standard

Cartridge Type
Single Cartridge System

LCD Display
5-row backlit LCD

Maximum Monthly Print Volume
Up to 8,000 pages per month

Language
English, French, Spanish, Portuguese

Features and specifications are subject to change without notice.

Ordering Information

FAXPHONE and Accessories

FAXPHONE® L100	5258B001AA
Cartridge 128 (yields approx. 2,100 pages based on ISO/IEC Standard)	3500B001AA
FAXPHONE® L100 Virtual CarePAK	6521A098AA
(2 Year Carry-in/Exchange CarePAK)	
FAXPHONE® L100 e-CarePAK	5707B025AA
(2 Year Carry-in/Exchange CarePAK)	

For More Information Visit

www.usa.canon.com/consumer
For the name of the nearest dealer, call:
1-800-OK-CANON

Canon U.S.A., Inc.
One Canon Plaza, Lake Success, NY 11042
1-800-OK-CANON

1 The Public Switched Telephone Network currently supports fax modem speeds of 28.8Kbps or lower, depending on telephone line conditions. Sending and receiving fax machines need to conform to ITU-T v.34 guidelines.
2 Based on ITU-T #1 Chart (standard mode).
3 Letter size, after being restored from Energy Saver mode.
4 Based on 20 lb. bond paper.
5 USB 2.0 Hi-Speed requires Windows® 7, Windows Vista®, Windows XP/2000 or Mac OS X operating systems. For Windows 98, Me and Mac OS X v. 10.2 to 10.2.6 operating systems, the printer/scanner will operate at USB 1.1 specifications.
6 Mac® OS X 10.4.9 and up and Linux® OS (print only) compatability to be announced; visit usa.canon.com for driver download availability.
7 Warranty program is subject to certain conditions and restrictions. See the warranty card for details.

Canon
*image*ANYWARE

0164W257