

## 12 Cup Pourover Coffee Brewer with 2 Warmers



### Features

#### 12 Cup Pourover Coffee Brewer

- Brews 3.8 gallons (14.4 litres) of per hour.
- Internal components are constructed from stainless steel.
- Pourover brewer requires no plumbing – completely portable.
- Just pour cold water in top and coffee brews immediately.
- Two separately controlled warmers.
- Integral part of any office coffee service program.
- SplashGard® funnel deflects hot liquids away from the hand.

### VPR

(decanters not included  
with some models)

Dimensions: 20.7" H x 16.2" W x 8" D  
(52.6cm H x 41.15cm W x 20.3cm D)

For current specification sheets and other information, go to [www.bunn.com](http://www.bunn.com).

### Related Products

#### Paper Filter Pack

Product No. : 20115.0000

Packed per case: 1,000

Dimensions: 4<sup>1</sup>/<sub>4</sub>" Base x 2<sup>3</sup>/<sub>4</sub>" Sidewall  
10.8 cm Base x 6.98 cm Sidewall



#### WX1-warmer

Product No. : 06450.0004

One position warmer



#### WX2-warmer

Product No. : 06310.0004

Two position warmer



#### Easy Pour® black decanter

Product No. : 06100.0101

Quantity: 1 (also packaged in  
quantities of 2, 3, 6, 12, & 24)



#### Easy Pour® orange decanter (for decaf)

Product No. : 06101.0101

Quantity: 1 (also packaged in  
quantities of 2, 3, 6, 12, & 24)



#### Model

#### Agency Listing

VPR



## Dimensions & Specifications

Model	Product #	Volts	Amps	Tank Heater Watts	Total Watts	Brewing Capacity	Cu. Ft.	Shipping Weight	Cord Attached
VPR-Black	33200.0000	120	13.1	1320	1575	3.8 gal./hr.	4.3	23 lbs.	Yes <sup>†</sup>
VPR-Black*	33200.0015	120	13.1	1320	1575	3.8 gal./hr.	4.1	24 lbs.	Yes <sup>†</sup>
VPR-Black**	33200.0002	120	13.1	1320	1575	3.8 gal./hr.	4.2	24 lbs.	Yes <sup>†</sup>

\* Model includes 2 glass decanters.

\*\*Model includes 2 Easy Pour® decanters.

<sup>†</sup>Power cord (NEMA 5-15P) 15 Amp-120V machine only.

**Brewing capacity:** based upon incoming water temp of 60°F (140°F rise) per 1/2 gallon brew time of 4 minutes.

**Electrical:** Model requires 2-wires plus ground service rated 120V, single phase, 60 Hz.

**Plumbing:** Tank capacity: 155 ounces (4.6L)

