



## CP750LCD Intelligent LCD UPS

Offers significant energy savings, battery backup and surge protection.

The CyberPower Intelligent LCD Series CP750LCD uninterruptible power supply (UPS) safeguards PCs and other electronics (monitors, cable/DSL modems, VoIP routers, and home theater devices) from blackouts, brownouts, surges, spikes, sags, and other power abnormalities.

This UPS system is ENERGY STAR® qualified and utilizes GreenPower UPS™ high-efficiency design to save on energy costs by reducing energy consumption and heat buildup. The multifunction diagnostic LCD provides users the ability to check UPS operating status and assist in trouble-shooting power anomalies.

A Three-Year Warranty ensures that this UPS has passed our highest quality standards in design, assembly, material or workmanship and further protection is offered by a \$150,000 Connected Equipment Guarantee.

### Typical Applications

- Desktop Computers
- Home Networking/VoIP
- Personal Electronics
- Home Theater Device

### Features

- 750VA / 420W
- Standby Topology
- Multifunction LCD Screen
- GreenPower UPS™
- ENERGY STAR® Qualified
- Full-time Surge Protection and Battery Backup
- Desktop Form Factor
- 8 Outlets / USB Port / RJ11 Protection
- PowerPanel® Personal Edition
- 3-Year Warranty

# CP750LCD Intelligent LCD UPS

Offers significant energy savings, battery backup and surge protection.

GENERAL	
UPS Topology	Standby
ENERGY STAR® Qualified	Yes
Energy Saving	GreenPower UPS™ High-Efficiency
INPUT	
Voltage	120 VAC
Frequency Range	47 – 63 Hz
Plug Type	NEMA 5-15P
Plug Style	Right Angle, 45° Offset Right
Cord Length	5 ft.
OUTPUT	
VA	750 VA
Watts	420 W
On Battery Voltage	120 VAC ± 5%
On Battery Frequency	50/60 Hz ± 1%
On Battery Waveform	Simulated Sine Wave
Outlet Type	NEMA 5-15R
Outlets – Total	8
Outlets – Battery & Surge Protected	4
Outlets – Surge-Only Protected	4
Outlets – Widely Spaced	2
Overload Protection	Internal Circuitry Limiting Circuit Breaker
BATTERY	
Runtime at Half Load (min)	10
Runtime at Full Load (min)	3
Battery Type	Sealed Lead-Acid
Battery Size	12V/7Ah
Battery Quantity	1
Typical Recharge Time	8 hours
SURGE PROTECTION & FILTERING	
Surge Suppression	890 J
Phone Protection RJ11	1-In, 2-Out
Coaxial Protection RG6	None
EMI/RFI Filtration	Yes

MANAGEMENT & COMMUNICATIONS	
Multifunction LCD Panel	Displays: Current/Load Level Runtime Battery Level Input Voltage Output Voltage Battery In Use Overload Silent Mode Normal Mode
HID Compliant USB Port	Yes
Management Cable	USB Cable
LED Indicators	Power On Wiring Fault
Audible Alarms	On Battery Low Battery Overload
Software	PowerPanel® Personal Edition
SILENT MODE	
Form Factor	Compact
Keyhole Mounting Slots	Yes
Dimensions – W×H×D (in)	10.4 × 6.9 × 3.1
Weight (lbs)	6.7
ENVIRONMENTAL	
Operating Temperature	32 – 104 °F (0 – 40 °C)
Operating Humidity	0 – 90% (non-condensing)
CERTIFICATIONS	
Safety	UL1778 cUL CSA C22.2 No. 107.3 FCC DOC Class B
Environmental	RoHS Compliant
WARRANTY	
Product Warranty	3 Years Limited
Connected Equipment Guarantee	Lifetime
CEG Amount	\$150,000