

1 Port USB to Null Modem RS232 DB9 Serial DCE Adapter Cable with FTDI

StarTech ID: ICUSB232FTN



The ICUSB232FTN FTDI USB to Null Modem Serial Adapter Cable (1-Port) converts an available USB 1.1 or 2.0 port into an RS232 Null Modem serial DB9 port, solving DCE/DTE conflicts directly, without requiring additional cross-wired serial cables or adapters.

This compact adapter features COM retention, allowing the same COM port value to automatically be re-assigned to the port if the cable is disconnected and re-connected to the host computer, or if the system is rebooted. The integrated FTDI chipset supports additional customization, advanced features, and compatibility not necessarily offered by other solutions.

The USB to Null Modem adapter is compatible with a broad list of operating systems including Windows®, Windows CE, Mac OS and Linux, making it easier to integrate into mixed environments.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect and program LED and Digital signage boards with serial communication ports
- Connect a satellite receiver, serial modem, or PDU

Features

- USB to Null Modem (Cross-Wired) RS232 Serial Adapter
- Integrated FTDI USB UART Chip
- Baud Rate up to 921.6Kbps
- COM Port assignments maintained across reboot
- USB-powered - no external power adapter required
- Compatible with USB 1.1 or 2.0 Ports
- Compatible with Windows®, Mac OS and Linux
- Single cable design for portability

Technical Specifications

Warranty	2 Years
Ports	1
Interface	USB 1.1
Interface	USB 2.0
Bus Type	USB 2.0
Chipset ID	FTDI - FT232RL
Connector Type(s)	1 - DB-9 (9 pin; D-Sub) Female
Connector Type(s)	1 - USB A (4 pin) Male
Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
Data Bits	7, 8
FIFO	256 byte Transmit, 128 byte Receive buffer
Parity	None, Odd, Even, Mark, Space
Stop Bits	1, 2
OS Compatibility	Windows® 7 (32/64bit), Vista(32/64), XP(32/64), 2000, CE(4.2+) Windows® Server 2008 R2/ 2003(32/64) Mac OS 9.x, 10.x Linux
Color	Black
Enclosure Type	Plastic
Cable Length	3.3 ft [1 m]
Product Length	7 in [179 mm]
Product Width	1.3 in [33.5 mm]
Product Height	0.6 in [16.5 mm]
Product Weight	3.1 oz [88 g]
Power Adapter Included	USB Powered
Operating Temperature	0°C to 55°C (32°F to 131°F)
Storage Temperature	-20°C to 85°C (32°F to 185°F)
Humidity	5~95% RH
System and Cable Requirements	One available USB 1.1 (or better) port
Shipping (Package) Weight	0.5 lb [0.2 kg]
Included in Package	1 - USB to RS-232 Null Modem Adapter
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

