

2 Port Triple Monitor DVI USB KVM Switch with Audio & USB 2.0 Hub

Product ID: SV231TDVIUA



The SV231TDVIUA 2-Port Triple Monitor DVI USB KVM Switch allows 2 PCs (each with 3 DVI video outputs) to share monitors, 1 microphone and set of speakers, 1 keyboard and 1 mouse, as well as an additional USB 2.0 peripheral such as an external hard drive, thumb drive, printer, or webcam.

The Triple DVI KVM switch enables you to switch back and forth between 2 multi DVI PCs at the touch of a button, while maintaining professional-level video quality on all monitors at resolutions up to 1920x1200. The triple monitor DVI switch also features an integrated USB hub port which allows USB 2.0 peripherals to be shared between attached systems, eliminating duplicate peripheral costs and offering the convenience of sharing stored data between PCs.

The SV231TDVIUA 2-Port Triple Head DVI KVM Switch is TAA compliant and backed by a StarTech.com 3-year warranty with free lifetime technical support.

PLEASE NOTE: While the DVI connector on this KVM is DVI-I, the KVM only supports single-link DVI-D (digital only) video sources. It is recommended wherever possible to use DVI-D cables across all PC to KVM and KVM to console connections.

Certifications, Reports and Compatibility

Applications

- Switch three displays, mouse, keyboard, speakers, microphone, and one USB peripheral between two PCs
- Graphic design and Multimedia production applications
- Great for CAD/CAM operators using multiple monitor systems
- Financial/banking and Trading work stations, with multiple monitors

- High resolution medical imaging with multiple displays

Features

- Switch 3 monitors and peripherals between 2 PCs
- Supports high definition DVI resolutions on 3 monitors each up to 1920x1200
- Switch Audio devices independently
- Supports front panel push button and hot-key functions for computer selection
- OS independent; No software or drivers required
- All metal chassis for long-term durability
- Hub port supports High speed USB 2.0 devices
- HDCP compliant

Hardware

Warranty	3 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	DVI
Number of Monitors Supported	Yes
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No

Performance

On-Screen Display	No
DVI Support	Yes
IP Control	No
Hot-Key Selection	Yes



Maximum Digital Resolutions	1920x1200
Wide Screen Supported	Yes
Auto Scan	3, 8, 15 & 30 seconds
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys
MTBF	62,000 hours

Connector(s)

Console Interface(s)	DVI-I (29 pin) USB Type-A (4 pin) USB 2.0 3.5 mm Mini-Jack (3 Position)
Host Connectors	DVI-I (29 pin) USB B (4 pin) 3.5 mm Mini-Jack (3 Position)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

Note	While the DVI connector on this KVM is DVI-I, the KVM only supports single-link DVI-D (digital only) video sources. It is recommended wherever possible to use DVI-D cables across all PC to KVM and KVM to console connections.
------	--

Indicators

LED Indicators	Orange - PC Online Green - Active PC
----------------	---

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.8A



Output Voltage	12V DC
Output Current	1.5A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	18

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 60C (14F to 140F)
Humidity	0~80% RH

Physical Characteristics

Color	Black
Material	Steel
Product Width	6.3 in [15.9 cm]
Product Height	2.9 in [74 mm]
Product Depth	3.9 in [100 mm]
Weight of Product	31.8 oz [900 g]

Packaging Information

Package Length	9.4 in [24 cm]
Package Width	7.3 in [18.5 cm]
Package Height	3.7 in [95 mm]
Shipping (Package) Weight	3.1 lb [1.4 kg]

What's in the Box

Included in Package	2 Port Triple Display KVM
	Rubber Foot Pads



Universal Power Adapter (NA/UK/EU)

User Manual

****Product appearance and specifications are subject to change without notice.***

