

1U 4-Post Adjustable Server Rack Mount Shelf - 330lbs(150 kg) - 19.5 to 38in Adjustable Mounting Depth Universal Tray for 19" AV, Data & Network Equipment Rack - 27.5in Deep

Product ID: ADJSHELFHD



The ADJSHELFHD 1U 4-post Adjustable Heavy Duty Fixed Rack Mount Shelf lets you add a high-capacity, adjustable 1U shelf to virtually any standard 4-post 19-inch server rack or cabinet.

This heavy duty rackmount shelf can be adjusted from 19.5in to 38in (mounting depth) to fit your rack. Constructed using 1.0mm SPCC commercial grade cold-rolled steel, providing the ability to hold up to 150kg (330lbs) of equipment - a durable solution for storing large, non-rackmount pieces of equipment, heavy tools or peripherals in your rack or cabinet.

The ADJSHELFHD is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

- Supply additional storage space for heavy, mission critical hardware and non-rack mount equipment
- For use with all 19" wide Server Racks and Cabinets

Features

- UNIVERSAL 19" FIT: This server rack mount shelf is designed to fit any 19in 4-post server rack and has a fixed

surface depth of 27.56in, and an adjustable mounting depth range of 19.5-38in for your data, networking or other small-form tools / equipment

- **COMPACT DESIGN:** The adjustable rack shelf features a very compact form factor, making it ideal for non-rackmount equipment, tools and peripherals in your home, studio or office space
- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with SPCC commercial cold-rolled steel, the sturdy IT-grade cabinet shelf ensures long term durability and supports a total weight load of 330 lb / 150 kg
- **VERSATILE FUNCTIONALITY:** With a surface depth of 27.56in and adjustable mounting depth range of 19.5-38in, this shelf can work with any 19 inch cabinet or equipment rack; It provides additional storage space for your tools or A/V accessories
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this adjustable rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

| | |
|--------------------|------------------------------|
| Warranty | Lifetime |
| Frame Type | Steel |
| U Height | 1U |
| Cable Management | No |
| Industry Standards | EIA RS310-D |
| Mounting Options | Front Mount (Front and Rear) |

Performance

| | |
|------------------------------|---|
| Weight Capacity (Stationary) | 330.8 lb [150 kg] |
| General Specifications | Weight Capacity: Rev 01 - up to 175lbs / 80kg; Rev 02 or above - up to 330lbs / 150kg |

Physical Characteristics

| | |
|----------------|-------------------|
| Color | Black |
| Material | Steel |
| Rail Thickness | 0.0 in [1.0 mm] |
| Product Length | 27.6 in [70.0 cm] |
| Product Width | 19.0 in [48.3 cm] |
| Product Height | 1.7 in [4.4 cm] |

| | |
|------------------------|-------------------|
| Weight of Product | 13.7 lb [6.2 kg] |
| Maximum Mounting Depth | 38.3 in [97.4 cm] |
| Minimum Mounting Depth | 19.5 in [49.5 cm] |

Packaging Information

| | |
|---------------------------|-------------------|
| Package Quantity | 1 |
| Package Length | 20.9 in [53.0 cm] |
| Package Width | 30.5 in [77.5 cm] |
| Package Height | 4.3 in [11.0 cm] |
| Shipping (Package) Weight | 15.9 lb [7.2 kg] |

What's in the Box

| | |
|---------------------|---------------------------------------|
| Included in Package | 1 - 1U High Cap Adjustable Rack Shelf |
| | 1 - Instruction Manual |
| | 1 - 1U Shelf Body |
| | 2 - Front Mounting Brackets |
| | 2 - Rear Mounting Brackets |
| | 8 - M6x12 mm Screws |
| | 8 - M6 Cage Nuts |
| | 8 - M6 Plastic Washer |
| | 8 - M6x12mm Mounting Bracket Screws |

****Product appearance and specifications are subject to change without notice.***