

24 Port 0.5U Cat5e Patch Panel - RJ45 Ethernet Rackmount Cat 5e 110 Patch Panel

StarTech ID: PANELHU24



The PANELHU24 Rack Mount Cat5e patch panel condenses 24 ports into a 0.5U panel, making it an ideal solution for smaller installations.

Color coded for both T568A and T568B wiring, this network patch panel provides the perfect solution for any voice or LAN application and offers dual type IDC termination. For convenience, the port numbers are clearly marked on the front of each RJ45 port, offering a quick and easy way to identify cable runs.

Durably constructed of only top quality materials, this 24-port Ethernet patch panel is backed by StarTech.com's 2 year warranty.

Applications

- For installation in 19" rack/cabinets
- Suitable for applications that use 22-26 AWG solid state and standard network cables
- 1000BASE-T Gigabit Ethernet, 100BASE-TX Fast Ethernet, 10BASE-T Ethernet applications
- Voice, video and other applications

Features

- High impact plastic housing, flame retardant UL 94V-0
- Meets and exceeds ANSI/TIA-568-C.2, ISO/IEC 11801 and EN 50173-1 specifications
- Dual-type IDC headers, situated 180° relative to the RJ45 ports, terminated using 110-type punch tool
- Color coded for both T568A and T568B installations

Technical Specifications

Warranty	2 Years
Color	Black
Product Length	19 in [482 mm]
Product Weight	0.9 lb [0.4 kg]
Operating Temperature	-10~50°
Humidity	10~65%
Note	IDC Contact: 0.8mm thickness alloy, tin plating over nickel Jack Contact: phosphor bronze, gold over nickel
Shipping (Package) Weight	1.1 lb [0.5 kg]
Included in Package	1 - 24 Port 1/2U Rackmount Cat5e 110 Patch Panel
Included in Package	M5 Screws
Included in Package	M6 Screws
Included in Package	Zip Ties
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

