

Multiple Video Input with Audio to HDMI® Scaler Switcher - HDMI / VGA / Component

StarTech ID: VS721MULTI



The VS721MULTI Multiple Video Input to HDMI® Switcher enables users to switch between 7 different audio-video sources to a single HDMI-equipped display.

This versatile scaler/switcher is the perfect solution for combining and scaling analog video sources (RGB/YPbPr/YCbCr) with your digital HDMI® display, eliminating the cost of upgrading individual components (i.e. DVD player, PC, VCR, etc.).

An all-in-one multimedia solution, the video converter/switcher includes support for full high definition 1080p video resolution as well as digital and analog audio. Plus, the switch features RS232 remote serial control, and includes a convenient IR remote control for switching between video sources .

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Convert analog and digital video to HDMI® for a variety of applications such as switching between consumer electronics devices (e.g. Blu-ray Disc™ players, satellite receivers, video game consoles and other devices)

Features

- Supports analog PC Resolution input and output up to WUXGA (1920x1200) @ 60Hz
- HDMI® and HDCP compliant
- Supports analog HDTV RGB/YPbPr/YCbCr input, output up to 1080p @ 60Hz

Technical Specifications

Warranty	2 Years
Audio	Yes
Cabling	HDMI
Industry Standards	High Speed HDMI®, HDCP
Output Signal	HDMI
Ports	7
Connector A	3 - HDMI (19 pin) Female
Connector A	1 - VGA (15 pin; High Density D-Sub) Female
Connector A	1 - Component Video (3 x RCA) Female
Connector A	1 - S-Video (4 pin; Mini-DIN) Female
Connector A	1 - Composite Video (1 x RCA) Female
Connector A	3 - RCA Female
Connector A	1 - 3.5 mm Mini-Jack (3 Position) Female
Connector B	HDMI (19 pin) Female
Maximum Analog Resolutions	VGA: 1920x1200 YPbPr: 1920x1080
Maximum Digital Resolutions	1600x1200
Supported Resolutions	Support VGA mode 640x480, 720x400, 800x600, 848x480, 1024x768, 1152x864, 1280x720, 1280x768, 1280x800, 1280x960, 1280x1024, 1360x768, 1400x1050, 1440x900, 1440x1050, 1600x1200, 1680x1050, 1920x1080, 1920x1200
Supported Resolutions	Support YPbPR mode 720x480, 720x576, 720x480, 720x576, 1280x720, 1920x1080, 1920x1080
Wide Screen	Yes
Supported	
OS	Windows® 8 (32/64bit), 7 (32/64bit), Vista(32/64), XP(32/64), 2000
Compatibility	Windows® Server 2008 R2, 2003(32/64)
Color	Black
Enclosure Type	Aluminum
Product Height	1.8 in [45 mm]

Product Length	15.1 in [384 mm]
Product Weight	63.5 oz [1800 g]
Product Width	6.8 in [173 mm]
LED Indicators	1 - 1 - HDMI
LED Indicators	1 - 2 - HDMI
LED Indicators	1 - 3 - HDMI
LED Indicators	1 - 4 - VGA
LED Indicators	1 - 5 - YPbPr
LED Indicators	1 - 6 - CVSB
LED Indicators	1 - 7 - S-VIDEO
Center Tip Polarity	Positive
Input Current	0.6 A
Input Voltage	110 ~ 240 AC
Output Current	1.5 A
Output Voltage	12 DC
Plug Type	M
Power Adapter Included	Yes
Humidity	0% to 95% RH Non-Condensing
Operating Temperature	0°C to 70°C (32°F to 158°F)
Storage Temperature	-20°C to 85°C (-4°F to 185°F)
Shipping (Package) Weight	6 lb [2.7 kg]

Included in Package	1 - Multiple Format to HDMI® Audio Video Switch
Included in Package	1 - IR Remote Control
Included in Package	1 - Mounting Kit
Included in Package	1 - RS232 Serial Cable - 6 ft
Included in Package	1 - RS-232 Control Software CD
Included in Package	1 - NA / UK / EU Power Adapter
Included in Package	1 - User Manual

Certifications, Reports and Compatibility

