

## 4-Post 8U Hinged Wall-Mount Network Rack, 19" Open Frame Server Rack with 19.8in Mounting Depth, Wall Mount Swing Out Data Rack for IT / AV / Patch Panel / Computer Equipment - TAA Compliant

**Product ID:** RK819WALLOH



The RK819WALLOH 8U Hinged Open Frame Wall Mount Server Rack lets you wall mount your (19-inch wide) servers, A/V or network equipment and features a hinged rack design that allows the entire frame to swing open for easy installation and maintenance of your equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The 8U wallmount rack offers a 4 post design for additional support of your equipment, storing a maximum weight capacity of 63 kg (139 lbs) with a maximum mounting depth of 19.8inch. Constructed of high-quality SPCC cold-rolled steel for strength and durability, the open frame wallmount server rack allows for maximum airflow, and ships complete with all of the rack screws and cage nuts required to mount your equipment, saving the expense of purchasing them separately.

### Certifications, Reports and Compatibility



### Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mount Audio/Video broadcast or distribution components

## Features

- **4-POST 8U HINGED WALL-MOUNT RACK:** IT Server Rack with 19.8in (50.2cm) maximum mounting depth is ideal for installing network switches out of the way (for example high up on a wall) in your warehouse, office, server room or store location
- **OPTIMIZED DESIGN:** The Wall Mount Data Rack features a hinged open frame rack design that allows the entire frame to swing open for easy installation and maintenance; Unobstructed airflow helps to keep your Data / AV / IT equipment cool
- **BUILT TO LAST:** The 8U wall mount computer equipment rack offers a 4 post design for additional support of your equipment; Constructed of high-quality SPCC cold-rolled steel for strength and durability with a maximum weight capacity of 139lbs (63kg)
- **FULLY ASSEMBLED:** The hinged server rack ships fully assembled with all of the rack screws and cage nuts required to mount your equipment; Hinged Data Rack is TAA and EIA/ECA-310-E Compliant
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 8U wall mounted network rack is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	4-Post
Frame Type	Open Frame
U Height	8U
Special Features	Ships Fully Assembled Wall-Mountable
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

### Performance

Weight Capacity	139.7 lb [63.4 kg]
-----------------	--------------------

---

### Physical Characteristics

Color	Black
-------	-------

Construction Material      Steel

**Product Measurements**

Product Length	23.7 in [60.2 cm]
Product Width	21.9 in [55.5 cm]
Product Height	19.2 in [48.8 cm]
Weight of Product	33.3 lb [15.1 kg]
Maximum Mounting Depth	19.8 in [50.2 cm]

**Packaging Information**

Flat Pack (Assembly Required)	No
Package Length	26.0 in [66.0 cm]
Package Width	25.0 in [63.5 cm]
Package Height	21.6 in [54.8 cm]
Shipping (Package) Weight	39.0 lb [17.7 kg]

**What's in the Box**

Included in Package	1 - Hinged Wall Mount Rack
	24 - #10-32 Screws
	24 - #10-32 Cage Nuts
	1 - Instruction Manual

***\*Product appearance and specifications are subject to change without notice.***