



e2460Pda

61cm (24") LED MONITOR

Line:

Line:	Professional
Paneltype:	WLED
Monitor Size:	24"
Visible Screen Size:	61cm
Screen Format:	16:9
Brightness:	250 (typ) cd/m ²
Contrast Ratio Dynamic:	20.000.000:1 (DCR)
Contrast Ratio Typical:	1.000:1
Pixel / Dot / Pitch:	0.276 (H) x 0.276 (V)
Display Area:	531.36 (H) x 298.89 (V)
Viewing Angle:	170°/ 160 (CR 10)
Response Time:	5 ms

Scanning Frequency:

Scanning Frequency:	H: 30-83 KHz/ V: 55-75Hz
Pixel Frequency:	148.5 MHz

Resolution:

Maximum Resolution:	1920 x 1080@60 Hz
Recommend Resolution:	1920 x 1080@60 Hz
Colors:	16.7
HDCP compatible:	Yes

Signal Input:


Analogue Input: D-Sub:	Yes
Digital Input: DVI-D / HDMI:	Yes / No
Composite CVBS Input:	No
Component CVBS Input:	No
S-Video Input:	No
Component Input:	No
SCART:	No
CI Card:	No
Display Port Input:	No

Connectors:

D-Sub 15 pin:	Yes
DVI-D 24-pin:	Yes
HDMI:	No
Display Port Input:	No

Power:

Power Source:	90 ~ 240 VAC, 50/60 Hz
Power Consumption:	On: 19.2W, Standby: <0.5W, Off: 0.3W





e2460Pda

61cm (24") LED MONITOR

Tuner System:

-

Other Features:

User Control:	Button
Speaker:	Yes
Wallmount:	Yes
Height adjustment:	Yes
Pivot:	Yes
Swivel:	Yes
Regulations:	CE Energy Star 5.0 EPEAT Gold EuP FCC GOST ISO 9241-307 NRTL RoHS TCO 6.0 TÜV-GS

Other Features:	-5/20 Tilt 90° Pivot 130 mm Height Adjustment DCR Eco Mode e-Saver e-Sensor i-Menu Kensington Security Lock Screen+ VESA 100 mm
-----------------	---

Accessoires:

Accessoires:	Power cable D-Sub cable DVI-D cable Audio cable Product CD Warranty Card on CD-ROM
--------------	---

Dimensions:

Dimensions (WxHxD):	565.4 x 393.6 (+130) x 244.58 mm
Weight:	6.54 kg w/o packaging // 8.55 kg w/ packaging
Warranty:	3 Years
EAN:	4038986141963

