



Powering Business Worldwide

Eaton 9PX 10kVA 120V Stepdown Transformer - 8 NEMA 5-20R, 2 L14-30R Outlets, 50/60 Hz, Hardwire Input, 3U Rack/Tower

MODEL NUMBER: 9PXTFMR11



10kVA transformer converts UPS 208V input to 120V for powering low-voltage AC components.

Features

208V to 120V Isolation Transformer Converts High-Voltage Input to Low-Voltage Output

This 10kVA Stepdown Transformer converts your UPS system's 208V high-voltage input to 120V low-voltage output. It features eight NEMA 5-20R and two L14-30R outlets for connecting equipment. Resettable circuit breakers protect your 120V equipment against overload conditions. The 9PXTFMR11 works with Eaton's 8kVA to 11kVA 9PX UPS systems.

Versatile Installation Options

You can mount the 9PXTFMR11 in 3U of space in an EIA-standard 19-inch rack using the included 4-post rail kit. You can also adapt it for tower installation using the included joining bracket and hardware.

Specifications

OVERVIEW	
UPC Code	743172039323
Accessory Type	Isolation Transformer
Accessory Class	UPS Accessories
INPUT	
Input Phase	Single-Phase
UPS Input Connection Type	Hardwire
Plug Type	Hard-wire
OUTPUT	

Highlights

- Converts 208V AC input into 120V output for powering low-voltage equipment
- 8 NEMA 5-20R 120V outlets for connecting components with 5-15P or 5-20P plugs
- Resettable circuit breakers protect mission-critical equipment from hazardous overloads
- Requires hardwired connection to Eaton 9PX 8kVA to 11kVA UPS systems

System Requirements

Compatible with Eaton's 8kVA to 11kVA 9PX UPS systems

Package Includes

- 9PXTFMR11 10kVA 120V Stepdown Transformer
- Transformer cable
- (2) Cable glands
- Joining bracket and hardware for tower configuration
- Rack-mounting hardware
- Owner's manuals



Powering Business Worldwide

Individually Controllable Load Banks	No
BATTERY	
Expandable Runtime	No
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	3U
Unit Dimensions (hwd / in.)	23.430 x 12.720 x 38.460
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico)
Product Compliance	CE (Europe); ENERGY STAR Qualified; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Extended Service Plans	ADVANCED DEPOT EXCHANGE Service Part Number: 9SW5Y-11000UC Expedited parts coverage for 5 years Parts, electronics and UPS batteries coverage Next business day shipping Technical support ON-SITE 24X7, NEXT DAY RESPONSE (US ONLY) 2 YEAR UPGRADE: WUN72XXX-11000UC On-site expedited parts and labor coverage for first 2 years Parts, electronics and UPS batteries coverage Eaton on-site labor coverage 24x7 coverage, next day response Next day shipping Technical support 3 YEAR FLEX PLAN: FLN73XXX-11000UC On-site parts and labor coverage for years 3 to 5 Parts, electronics and UPS batteries coverage 24x7 on-site labor coverage, next day response Next day shipping Technical support

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.