

USB 3.0 SuperSpeed to SATA External Hard Drive Docking Station for 2.5in or 3.5in HDD

MODEL NUMBER: **U339-000**



Description

Tripp Lite's USB 3.0 SATA Hard Drive Dock gives you a quick and easy way to set up an external hard drive storage system. Plug the docking station into an available USB 3.0 port on your computer, then insert a 2.5" or 3.5" SATA drive for an instant external storage device. Transfer data at SuperSpeed USB 3.0 rates up to 5 Gbps (provided computer is USB3.0 capable). Far easier than installing the hard drive internally or in a caddy, the USB3.0/SATA Dock is easy to use, convenient and practical. Backward compatible to older USB 2.0 and 1.1 computers (480mbps and 12mbps transfer speeds respectively). Includes 100-240V AC Adapter, and 4-ft. (1.22 m) USB 3.0 cable. (No disk drives are included with this unit) Compatible with Windows (up to 10) and Mac.

Features

- Instant SATA external storage for 2.5" and 3.5" SATA drives
- Plug-n-Play (no software or configuring needed)
- USB 3.0 SuperSpeed transfer rates up to 5 Gbps
- Heavy-weighted base for stability
- Compatible with Windows (up to 10) and Mac

Specifications

OVERVIEW	
UPC Code	037332175588
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 12V, 2A

Highlights

- Plug in 2.5" or 3.5" SATA drives for instant external storage
- Plug and Play - no tools, software or configuration required
- Connect via USB 3.0 computer port
- Super Speed USB 3.0 - Up to 5 Gbps transfer speeds
- Compatible with Windows (up to 10) and Mac

System Requirements

- 2.5" or 3.5" SATA hard drive
- Computer with an available USB port. USB 3.0 port is required to achieve maximum speeds.
- Compatible with Windows (up to 10) and Mac

Package Includes

- U339-000 USB 3.0 SATA Hard Drive Dock
- USB 3.0 Device Cable
- External Power Supply with NEMA 1-15P Plug (100-240 VAC, 50/60Hz, 0.6A; Output: 12V, 2A)

Technology	USB 3.0 (SuperSpeed); SATA/eSATA; USB
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
Bus Powered	No
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A
External Power Supply Output Specs (V / A)	12V / 2A
External Power Supply Cord Length (ft.)	4.9
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; UL; cUL; RoHS
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (Power); Blue (Read, Write)
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	7.87 x 13.21 x 17.02
Shipping Dimensions (hwd / in.)	3.10 x 5.20 x 6.70
Shipping Weight (kg)	0.54
Shipping Weight (lbs.)	1.20
Unit Dimensions (hwd / cm)	5.8 x 13 x 7.6
Unit Dimensions (hwd / in.)	2.3 x 5.1 x 3
Unit Packaging Type	Box
Unit Weight (kg)	0.25
Unit Weight (lbs.)	0.55
ENVIRONMENTAL	
Operating Temperature Range	50 to 122 F (10 to 50 C)
Storage Temperature Range	32 to 149 F (0 to 65 C)
Relative Humidity	10% to 80% RH, Non-Condensing

BTUs	81.9 BTU/Hr
Power Consumption (Watts)	24
CONNECTIONS	
Ports	1
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>