2 Port High Resolution VGA Video Splitter with Audio - 400 MHz

Product ID: ST122PROA

This high resolution VGA splitter offers a practical solution for high-res multi-screen presentations, allowing a VGA video signal as well as the corresponding audio to be broadcast from a computer to up to two sets of VGA monitors and speakers simultaneously.

The VGA splitter is ideal for classrooms, tradeshows, in-store displays or any application where high quality video and audio is required, supporting displays with up to 400 MHz of video bandwidth and high resolution applications up to 2048 x 1536.

To help ensure high quality VGA video even at longer distances, the high resolution VGA splitter features a built-in booster circuit that allows monitors to be located up to 210ft away from the host system.

Designed for simplicity and convenience, the VGA splitter offers easy plug and play installation; a completely hardware-based solution, the VGA splitter requires no software operation, saving both time and hassle.

Backed by our 2-year warranty and free lifetime technical support, this 2-port high-resolution VGA splitter lets you get the most out of your video content with quality construction you can depend on.

Certifications, Reports and Compatibility

Applications

• In-store product merchandising

• Information booths/kiosks

• Trade-shows

• Lecture halls and classrooms

• Airports, bus terminals and train stations

Features

• Compatible with VGA, SVGA and Multisync monitors

• 400 MHz bandwidth provides brilliant 2048 x 1536 resolution

• DDC, DDC2 & DDC2B compatible (on Video Out port 1)

• Includes DC 7.5V power adapter

• Daisy chainable for almost unlimited expansion

• Uses standard monitor extension cables (StarTech.com coaxial VGA cables recommended for best picture quality)

Hardware		
	Warranty	2 Years
	Ports	2
	AV Input	VGA
	AV Output	VGA
	Audio	Yes

Performance		
	Maximum Analog Resolutions	2048x1536 @ 60Hz
	Bandwidth	400MHz

Connector(s)		
	Connector A	VGA (15 pin, High Density D-Sub)
		3.5 mm Mini-Jack (3 Position)
	Connector B	VGA (15 pin, High Density D-Sub)
		3.5 mm Mini-Jack (3 Position)

Special Notes / Requirements		
	Note	Units made before August 2008 shipped with AC 7.5V 800mA power adapter

Power

	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Output Voltage	12V DC
	Output Current	0.6A
	Power Consumption (In Watts)	7.2

Physical Characteristics

	Color	Gray
	Product Length	5.1 in [13.0 cm]
	Product Width	3.0 in [75.0 mm]
	Product Height	2.8 in [72.0 mm]
	Weight of Product	15.8 oz [447.0 g]

Packaging Information

	Package Length	6.2 in [15.7 cm]
	Package Width	9.6 in [24.4 cm]
	Package Height	2.6 in [67.0 mm]
	Shipping (Package) Weight	25.2 oz [715.0 g]

What's in the Box

	Included in Package	2 Port VGA Splitter
		Power Adapter
		Instruction Manual

*Product appearance and specifications are subject to change without notice.