

HSM SECURIO C18

personal shredder

Compact shredder for personal or home office use



- Entry level personal/home office model designed for 1 to 3 users
- Automatic start/stop via photo eye sensor
- Separate reverse button
- LED indicates machine status as well as container full, cutting unit blocked, container open and safety element pressed
- Cutting rollers are V-TEK technology by HSM with specially hardened steel rollers that save valuable energy
- Bin level capacity can be seen through inspection window
- Automatic stop when the shredded material is removed
- Quiet operation sound minimizes noise development in the workplace
- Energy Management Control System EcoSmart: particularly low power consumption of 0.1 watt in standby mode
- Anti-Jam Technology designed to easily and quickly reverse out paper in the event the machine is overloaded
- Uses an 11 gallon capacity shred bag; Part #HSM1310



HSM part#	HSM1910	HSM1911	HSM1913	HSM1912
Cutting type	Strip cut	Strip cut	Cross cut	Micro cut
Cutting size	1/8"	1/4"	1/8" x 1 1/8"	1/16" x 9/16"
Security level DIN 32757-1	2	2	3	4
Security level DIN 66399	P-2 / T-2 / E-2	P-2 / O-2 / T-2 / E-2	P-4 / T-4 / E-3 / F-1	P-5 / T-5 / E-4 / F-2
Cutting capacity per run in sheets	14 - 15	19 - 20	10 - 11	8 - 9
Cutting speed	10.67 ft / min	10.67 ft / min	10.67 ft / min	10.67 ft / min
Throat opening	9.1"	9.1"	9.1"	9.1"
Motor at max. no. of sheets	400W	400W	400W	400W
Motor power (horsepower)	0.54	0.54	0.54	0.54
Voltage	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz
Dimensions (H x W x D)	21.3" x 14.4" x 11.3"	21.3" x 14.4" x 11.3"	21.3" x 14.4" x 11.3"	21.3" x 14.4" x 11.3"
Weight	21.6 lbs	21.6 lbs	25.1 lbs	25.1 lbs
Shred-bin volume	6.6 gallons	6.6 gallons	6.6 gallons	6.6 gallons
Cutting capabilities				

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
 419 Boot Road
 Downingtown, PA 19335
 www.hsmofamerica.com
 Customer Service / 800.613.2110

HSM[®]
 Great Products, Great People.