


HSM SECURIO P40i

Professional shredder

Large Volume, High Performance



- High quality materials and “Made in Germany” quality for safety and durability.
- Cutting rollers made of hardened steel rollers.
- Integrated automatic oiler provides consistently high cutting capacity (HSM1883, HSM1882, HSM1885).
- The innovative drive and operating concept IntelligentDrive offers silent, standard and performance operating modes for destroying data efficiently.
- Intuitive operation and menu selection via the high resolution touch display
- Powerful motor allows for continuous operation
- Uses Energy Management Control System (EMCS) to deal with energy in a sensible manner by reducing energy consumption up to 90%
- Anti-Jam technology. The machine recognizes very quickly if too much paper has been fed in and reacts autonomously.
- The device automatically switches off if pressure is applied to the safety element.
- Light barrier for automatic start/stop.
- Mobile on castors.
- The button lock feature prevents unintentional use.
- High quality wooden floor cabinet with door.
- Level indicator through inspection window.
- Uses a 58 gallon capacity shred bag; Part #HSM2117



HSM part #	HSM1880	HSM1881	HSM1883	HSM1882	HSM1885
Cutting type	Strip cut	Strip cut	Cross cut	Micro cut	High Security P-6
Cutting size	1/8"	1/4"	3/16" x 1 1/8"	1/16" x 9/16"	1/32" x 7/16"
Security level DIN 32757-1	2	2	3	4	5
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-2 / O-2 / T-2 / E-2	P-4 / O-3 / T-4 / E-3 / F-1	P-5 / O-4 / T-5 / E-4 / F-2	P-6 / F-3
Cutting capacity per run in sheets	45-47 [^]	58-60 [^]	35-37 [^]	22-24 [^]	13-14 [^]
Cutting speed	18 ft/min	18 ft/min	18 ft/min	18 ft/min	18 ft/min
Throat Opening	13"	13"	13"	13"	13"
Motor power (hp)	2.82	2.82	2.82	2.82	2.82
Voltage	115V / 60Hz	115V / 60Hz	115V / 60Hz	115V / 60Hz	115V / 60Hz
Dimensions (HxWxD)	36.9" x 23.5" x 22.5"	36.9" x 23.5" x 22.5"	36.9" x 23.5" x 22.5"	36.9" x 23.5" x 22.5"	36.9" x 23.5" x 22.5"
Weight	158 lbs	158 lbs	158 lbs	158 lbs	158 lbs
Shred-bin volume	40 gallons	40 gallons	40 gallons	40 gallons	40 gallons
Cutting capabilities					

All technical specifications are approximate values. Technical and design modifications reserved.

[^]Sheet capacity will vary depending on paper size, weight, quality and proper power supply

HSM of America, LLC
 419 Boot Road
 Downingtown, PA 19335
 www.hsmofamerica.com
 Customer Service: 800.613.2110



Great Products, Great People.