

3m Cisco Compatible SFP+ 10-Gigabit Ethernet (10GbE) Twinax Direct Attach Cable

StarTech ID: SFPCMM3M



The SFPCMM3M Cisco Compatible 3m SFP+ cable is a fully hot pluggable, direct attach cable, supporting 10 Gigabit Ethernet and Fiber Channel applications connected through (Small Form Factor Pluggable) SFP+ ports.

Designed for short length, high speed interconnects, this low power, low latency Twinax cable is a cost-effective alternative to fiber optic cable assemblies and is intended for short distance applications such as point-to-point in-rack and across rack network switch/server connections.

Backed by our 2-year warranty, this 10GBASE-CU SFP+ Cable is compliant with MSA (Multi-Source Agreement) standards, making it a reliable replacement SFP-H10GB-CU3M cable.

Applications

- Use in 10Gb Ethernet and Fiber Channel applications
- Point-to-point in-rack and across rack network switch/server connections (Storage Area Networks (SAN), Network Attached Storage (NAS), Storage Servers, etc.)

Features

- Compatible with Cisco equipment
- Compliant with SFP+ MSA Multi-Source Agreement standards
- Support for 1x, 2x, 4x and 8x Fiber Channel data rates
- Compliant with SFF 8431 connector standards
- 30AWG, 100 Ohm impedance
- Support for multi-gigabit data rates up to 10.5Gbps
- Hot-swappable with fiber optic modules
- Low Power consumption <0.5W
- Quick release latching SFP+ connectors

Technical Specifications

Warranty	2 Years
Cable Jacket Type	PVC - Polyvinyl Chloride
Connector A	1 - SFP+ Latching Plug
Connector B	1 - SFP+ Latching Plug
Impedance	100 Ohm
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3 m]
Product Weight	0.3 lb [0.1 kg]
Wire Gauge	30 AWG
Operating Temperature	01/7/2013egC to 701/7/2013egC
Storage Temperature	-401/7/2013egC to 801/7/2013egC
Package Quantity	1
Shipping (Package) Weight	0.3 lb [0.1 kg]
Included in Package	1 - 3m SFP+ 10-Gigabit Ethernet (10GbE) Twinax Cable

Certifications, Reports and Compatibility

