



Part Number BRT060-10
 Basic, Non-Surge
 Power Configuration 15A, 120V, 1.4kW
 Physical Configuration 19 in / 483 mm Horizontal



Description	The BRT060-10 non-surge unit is ideal for facilities already equipped with surge protection.
Product Summary	BRT060-10 - Non-Surge, 15A, 120V, Horizontal, (6) NEMA 5-15R, power switch, breakered, 10 ft power cord with 5-15P
Monitoring	None
Plug Form	 5-15P
Receptacle	 NEMA 5-15R (Quantity: 6)

BRT060-10 - Product Specification and Options

Quantity Of Inputs	1
Voltage	120V
Current	15A
VA per Input (Load Capacity)	1.4kW
Frequency	50/60 Hz
Over Current Protection	15A Thermal Breaker
Switch	Yes
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	14/3
Power Cable Length	10ft
Plug Type	NEMA 5-15P
Receptacle/Socket Type #1	NEMA 5-15R
Quantity on Rear #1	6
Center to Center Receptacle Spacing	2.5
Quantity per Breaker #1	6
Style #1	Individual - Transformer Spaced
Maximum Output per Receptacle/Socket #1	15A
Voltage per Receptacle/Socket #1	120V
Heavy Steel -Black Powder Coat	Yes
Configuration	19in / 435mm Horizontal Rackmount
Flush Mount	Yes
Made in the USA	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 3.75in
Shipped Weight	6lbs (2.72kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geisteurope.com

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com

Geist Asia

Hong Kong
Tel: +852 90361927
Email: salesasia@geistglobal.com