



Part Number BRX080-10  
 Basic, Non-Surge  
 Power Configuration 15A, 120V, 1.4kW  
 Physical Configuration 19 in / 483 mm Horizontal



Description	The BRX080-10 non-surge unit is ideal for facilities already equipped with surge protection.
Product Summary	BRX080-10 - Non-Surge, 15A, 120V, Horizontal, (8) NEMA 5-15R, power switch, breakered, 10 ft power cord with 5-15P
Monitoring	None
Plug Form	 5-15P
Receptacle	 NEMA 5-15R (Quantity: 8)



## BRX080-10 - Product Specification and Options

Quantity Of Inputs	1
Voltage	120V
Current	15A
VA per Input (Load Capacity)	1.4kW
Frequency	50/60 Hz
Over Current Protection	15A Thermal Breaker
Switch	Yes
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	14/3
Power Cable Length	10ft
Plug Type	NEMA 5-15P
Receptacle/Socket Type #1	NEMA 5-15R
Quantity on Face #1	4
Quantity on Rear #1	4
Center to Center Receptacle Spacing	3.2
Quantity per Breaker #1	8
Style #1	Individual - Transformer Spaced
Maximum Output per Receptacle/Socket #1	15A
Voltage per Receptacle/Socket #1	120V
Heavy Steel -Black Powder Coat	Yes
Configuration	19in / 435mm Horizontal Rackmount
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 4.50in
Shipped Weight	6lbs (2.72kg)

### Geist Americas

1821 Yolande Ave  
Lincoln, NE 68521 USA  
1.800.432.3219 or  
1.402.474.3400  
www.geistglobal.com

### Geist Europe

Unit 1, The Monarch Centre,  
Venture Way,  
Priorswood, Taunton,  
Somerset, TA2 8DE UK  
+44 (0) 1823 275100  
www.geisteurope.com

### Geist Asia

China  
Tiley Plaza Bldg. A, Unit #2808,  
No. 199 Haide 3 Road,  
Nanshan Shenzhen,  
Guangdong Province, China.  
Postal Code: 518000  
Tel: +86.755.86639505  
www.geistglobal.com

### Geist Asia

Hong Kong  
Tel: +852 90361927  
Email: salesasia@geistglobal.com