



Part Number SPCN104-10
 Basic, Surge
 Power Configuration 15A, 120V, 1.4kW
 Physical Configuration 19 in / 483 mm Horizontal



| | |
|-----------------|---|
| Description | SPCN104-10 is ideal for smaller environments that don't have protective surge suppression at the facility level, or just when additional protection is needed. Parallel circuitry keeps the SPCN104-10 working as a power strip, even if a surge or spike disables surge suppression. |
| Product Summary | SPCN104-10 - Surge, 15A, 120V, Horizontal, (10) NEMA 5-15R, breakered, 10 ft power cord with 5-15P, Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input, , Aggregate - Total Unit Monitoring |
| Monitoring | Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input |
| Plug Form |  5-15P |
| Receptacle |  NEMA 5-15R (Quantity: 10) |



SPCN104-10 - Product Specification and Options

| | |
|---|---|
| Monitoring | Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input |
| Monitoring Level 1 | Aggregate - Total Unit Monitoring |
| Quantity Of Inputs | 1 |
| Voltage | 120V |
| Current | 15A |
| VA per Input (Load Capacity) | 1.4kW |
| Frequency | 50/60 Hz |
| Over Current Protection | 15A Thermal Breaker |
| Switch | No |
| Indicators - LED(s) | 1 - Power ON Green LED |
| Power Cable Wire Gauge | 14/3 |
| Power Cable Length | 10ft |
| Plug Type | NEMA 5-15P |
| Receptacle/Socket Type #1 | NEMA 5-15R |
| Quantity on Rear #1 | 10 |
| Quantity per Breaker #1 | 10 |
| Style #1 | Duplex |
| Maximum Output per Receptacle/Socket #1 | 15A |
| Voltage per Receptacle/Socket #1 | 120V |
| Joule Rating | 720 |
| UL 1449 Rating (500A) | 330V |
| Clamping Level | < 315V |
| Response Time | < 5 nanoseconds |
| Technology Used | Super MOVs |
| Surge Indicator Red LED | Yes |
| Heavy Steel -Black Powder Coat | Yes |
| Configuration | 19in / 435mm Horizontal Rackmount |
| Configuration | 70in / 1782mm Vertical Rackmount |
| Flush Mount | Yes |
| Made in the USA | Yes |
| Product Warranty | Three Year |
| Connected Equipment Warranty | Three Year - \$5000 |
| Certification/Agency Approvals | RoHS Compliant |
| Certification/Agency Approvals | UL & c-UL Listed 60950 |
| Chassis Dimensions (HxWxD) | 1.72in x 17in x 4.50in |
| Shipped Weight | 7lbs (3.18kg) |

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,

Geist Asia

Hong Kong
Tel: +852 90361927

1.402.474.3400
www.geistglobal.com

Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geisteurope.com

Nanshan Shenzhen,
Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com

Email: salesasia@geistglobal.com