

Part Number	BR120-1020TL
	Basic, Non-Surge
Power Configuration	20A, 120V, 1.9kW
Physical Configuration	19 in / 483 mm Horizontal



Description	The BR120-1020TL non-surge unit is ideal for facilities already equipped with surge protection.
Product Summary	BR120-1020TL - Non-Surge, 20A, 120V, Horizontal, (12) NEMA 5-15R, power switch, breakered, 10 ft power cord with L5-20P
Monitoring	None
Plug Form	 L5-20P
Receptacle	 NEMA 5-15R (Quantity: 12)

BR120-1020TL - Product Specification and Options

Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60 Hz
Over Current Protection	20A Thermal Breaker
Switch	Yes
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA L5-20P Twistlock
Receptacle/Socket Type #1	NEMA 5-15R
Quantity on Face #1	2
Quantity on Rear #1	10
Style #1	Duplex
Maximum Output per Receptacle/Socket #1	15A
Voltage per Receptacle/Socket #1	120V
Heavy Steel -Black Powder Coat	Yes
Configuration	19in / 435mm Horizontal Rackmount
Flush Mount	Yes
Made in the USA	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 3.75in
Shipped Weight	6lbs (2.72kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geisteurope.com

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com

Geist Asia

Hong Kong
Tel: +852 90361927
Email: salesasia@geistglobal.com