




Part Number BRA100-1025TL  
 Basic, Non-Surge  
 Power Configuration 20A, 120V, 1.9kW  
 Physical Configuration 19 in / 483 mm Horizontal



|                 |   |
|-----------------|---|
| Description     | The BRA100-1025TL non-surge unit is ideal for facilities already equipped with surge protection.  |
| Product Summary | BRA100-1025TL - Non-Surge, 20A, 120V, Horizontal, (10) NEMA 5-20R, power switch, breakered, 10 ft power cord with L5-20P, Current - Local<br><br>Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input , Aggregate - Total Unit Monitoring |
| Monitoring      | Current - Local<br><br>Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input   |
| Plug Form       |  L5-20P  |
| Receptacle      |  NEMA 5-20R (Quantity: 10)   |



## BRA100-1025TL - Product Specification and Options

|   |   |
|---|---|
| Monitoring                              | Current - Local<br>Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input |
| Monitoring Level 1                      | Aggregate - Total Unit Monitoring   |
| Quantity Of Inputs                      | 1   |
| Voltage                                 | 120V  |
| Current                                 | 20A   |
| VA per Input (Load Capacity)            | 1.9kW   |
| Frequency                               | 50/60 Hz  |
| Over Current Protection                 | 20A Thermal Breaker   |
| Switch                                  | Yes   |
| Indicators - LED(s)                     | 1 - Power ON Green LED  |
| Power Cable Wire Gauge                  | 12/3  |
| Power Cable Length                      | 10ft  |
| Plug Type                               | NEMA L5-20P Twistlock   |
| Receptacle/Socket Type #1               | NEMA 5-20R  |
| Quantity on Rear #1                     | 10  |
| Quantity per Breaker #1                 | 10  |
| Style #1                                | Duplex  |
| Maximum Output per Receptacle/Socket #1 | 20A   |
| Voltage per Receptacle/Socket #1        | 120V  |
| Heavy Steel -Black Powder Coat          | Yes   |
| Configuration                           | 19in / 435mm Horizontal Rackmount   |
| Flush Mount                             | Yes   |
| Made in the USA                         | Yes   |
| Product Warranty                        | Three Year  |
| Certification/Agency Approvals          | RoHS Compliant  |
| Certification/Agency Approvals          | UL & c-UL Listed 60950  |
| Chassis Dimensions (HxWxD)              | 1.72in x 17in x 4.50in  |
| Shipped Weight                          | 8lbs (3.63kg)   |

### Geist Americas

1821 Yolande Ave  
Lincoln, NE 68521 USA  
1.800.432.3219 or  
1.402.474.3400  
www.geistglobal.com

### Geist Europe

Unit 1, The Monarch Centre,  
Venture Way,  
Priorswood, Taunton,  
Somerset, TA2 8DE UK  
+44 (0) 1823 275100  
www.geisteurope.com

### Geist Asia

China  
Tiley Plaza Bldg. A, Unit #2808,  
No. 199 Haide 3 Road,  
Nanshan Shenzhen,  
Guangdong Province, China.  
Postal Code: 518000  
Tel: +86.755.86639505  
www.geistglobal.com

### Geist Asia

Hong Kong  
Tel: +852 90361927  
Email: salesasia@geistglobal.com