

Part Number	JLCN082-102I44ST5
	Basic, Non-Surge
Power Configuration	20A, 120V, 1.9kW
Physical Configuration	17 in / 432 mm Horizontal/Vertical



Description	The JLCN082-102I44ST5 non-surge unit is ideal for facilities already equipped with surge protection.	
Product Summary	JLCN082-102I44ST5 - Non-Surge, 20A, 120V, Horizontal/Vertical, (4) IEC C13,(4) IEC C19, 10 ft power cord with 5-20P, Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input , Aggregate - Total Unit Monitoring	
Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input	
Plug Form	 5-20P	
Receptacle	 IEC C13 (Quantity: 4)  IEC C19 (Quantity: 4)	

JLCN082-102I44ST5 - Product Specification and Options

Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60 Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 5-20P
Combined Total Receptacle/Socket Quantity	8
Receptacle/Socket Type #1	IEC C13
Quantity on Face #1	4
Style #1	Banks of 2
Maximum Output per Receptacle/Socket #1	15A per receptacle bank
Voltage per Receptacle/Socket #1	120V
Receptacle/Socket Type #2	IEC C19
Quantity on Face #2	4
Style #2	Individual
Maximum Output per Receptacle/Socket #2	20A
Voltage per Receptacle/Socket #2	120V
Heavy Steel -Black Powder Coat	Yes
Configuration	17in Vertical/Horizontal Rackmount
19in Panel Mount Brackets	Yes
SLB-4 Brackets	Yes
Made in the USA	Yes
Product Warranty	Three Year
Certification/Agency Approvals	NOM-003-SCFI-2000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	17.0in x 1.72in x 1.85in
Shipped Weight	6lbs (2.72kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geisteurope.com

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.
Postal Code: 518000

Geist Asia

Hong Kong
Tel: +852 90361927
Email: salesasia@geistglobal.com

