



Part Number NSVBN200-102S20
Basic, Non-Surge
Power Configuration 20A, 120V, 1.9kW
Physical Configuration 66 in / 1682 mm Vertical



Description The NSVBN200-102S20 non-surge unit is ideal for facilities already equipped with surge protection.

Product Summary NSVBN200-102S20 - Non-Surge, 20A, 120V, Vertical, (20) NEMA 5-20R, breakerred, 10 ft power cord with 5-20P

Monitoring None

Plug Form  5-20P

Receptacle  NEMA 5-20R (Quantity: 20)



NSVBN200-102S20 - Product Specification and Options

Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60 Hz
Over Current Protection	20A Thermal Breaker
Switch	No
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 5-20P
Receptacle/Socket Type #1	NEMA 5-20R
Quantity on Face #1	20
Center to Center Receptacle Spacing	2.8
Quantity per Breaker #1	20
Style #1	Individual - In-Line
Maximum Output per Receptacle/Socket #1	20A
Voltage per Receptacle/Socket #1	120V
Heavy Steel -Black Powder Coat	Yes
Configuration	66in / 1682mm Vertical Rackmount
Plastic Mounting Clips	1 - Bottom; 2 - Top
Made in the USA	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 1.61in x 1.61in
Shipped Weight	9lbs (4.08kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geisteurope.com

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2910,
No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com

Geist Asia

Hong Kong
Tel: +852 81764860
Email: salesasia@geistglobal.com