



Part Number	SPFC104-1025 Basic, Surge
Power Configuration	20A, 120V, 1.9kW
Physical Configuration	19 in / 483 mm Horizontal



Description	SPFC104-1025 is ideal for smaller environments that don't have protective surge suppression at the facility level, or just when additional protection is needed. Parallel circuitry keeps the SPFC104-1025 working as a power strip, even if a surge or spike disables surge suppression.
Product Summary	SPFC104-1025 - Surge, 20A, 120V, Horizontal, (10) NEMA 5-20R, power switch, breakered, 10 ft power cord with 5-20P, Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input, , Aggregate - Total Unit Monitoring
Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Plug Form	 5-20P
Receptacle	 NEMA 5-20R (Quantity: 10)



## SPFC104-1025 - Product Specification and Options

Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60 Hz
Over Current Protection	20A Thermal Breaker
Switch	Yes
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 5-20P
Receptacle/Socket Type #1	NEMA 5-20R
Quantity on Face #1	10
Quantity per Breaker #1	10
Style #1	Duplex
Maximum Output per Receptacle/Socket #1	20A
Voltage per Receptacle/Socket #1	120V
Joule Rating	720
UL 1449 Rating (500A)	330V
Clamping Level	< 315V
Response Time	< 5 nanoseconds
Technology Used	Super MOVs
Surge Indicator Red LED	Yes
Heavy Steel -Black Powder Coat	Yes
Configuration	19in / 435mm Horizontal Rackmount
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	Three Year
Connected Equipment Warranty	Three Year - \$5000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 4.50in
Shipped Weight	8lbs (3.63kg)

### Geist Americas

1821 Yolande Ave  
Lincoln, NE 68521 USA  
1.800.432.3219 or  
1.402.474.3400  
www.geistglobal.com

### Geist Europe

Unit 1, The Monarch Centre,  
Venture Way,  
Priorswood, Taunton,  
Somerset, TA2 8DE UK  
+44 (0) 1823 275100

### Geist Asia

China  
Tiley Plaza Bldg. A, Unit #2808,  
No. 199 Haide 3 Road,  
Nanshan Shenzhen,  
Guangdong Province, China.

### Geist Asia

Hong Kong  
Tel: +852 90361927  
Email: salesasia@geistglobal.com

[www.geisteurope.com](http://www.geisteurope.com)

Postal Code: 518000  
Tel: +86.755.86639505  
[www.geistglobal.com](http://www.geistglobal.com)