



Part Number	VSSBC204-102R20TL Basic, Surge
Power Configuration	20A, 120V, 1.9kW
Physical Configuration	66 in / 1682 mm Vertical



Description	VSSBC204-102R20TL is ideal for smaller environments that don't have protective surge suppression at the facility level, or just when additional protection is needed. Parallel circuitry keeps the VSSBC204-102R20TL working as a power strip, even if a surge or spike disables surge suppression.
Product Summary	VSSBC204-102R20TL - Surge, 20A, 120V, Vertical, (20) NEMA 5-20R, power switch, breakered, 10 ft power cord with L5-20P, Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input, , Aggregate - Total Unit Monitoring
Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Plug Form	 L5-20P
Receptacle	 NEMA 5-20R (Quantity: 20)

VSSBC204-102R20TL - Product Specification and Options

Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60 Hz
Over Current Protection	20A Thermal Breaker
Switch	Yes
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA L5-20P Twistlock
Receptacle/Socket Type #1	NEMA 5-20R
Quantity on Face #1	20
Center to Center Receptacle Spacing	2.8
Style #1	Individual - Rotated
Maximum Output per Receptacle/Socket #1	20A
Voltage per Receptacle/Socket #1	120V
Joule Rating	720
UL 1449 Rating (500A)	330V
Clamping Level	< 315V
Response Time	< 5 nanoseconds
Technology Used	Super MOVs
Surge Indicator Red LED	Yes
Heavy Steel -Black Powder Coat	Yes
Configuration	66in / 1682mm Vertical Rackmount
Plastic Mounting Clips	1 - Bottom; 2 - Top
Made in the USA	Yes
Product Warranty	Three Year
Connected Equipment Warranty	Three Year - \$5000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 1.61in x 1.61in
Shipped Weight	9lbs (4.08kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.

Geist Asia

Hong Kong
Tel: +852 90361927
Email: salesasia@geistglobal.com

www.geisteurope.com

Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com