



## VSSBN204-102S20TL

**Part Number:** VSSBN204-102S20TL  
**Category:** Basic  
**Sub Category:** Surge  
**Power Configuration:** 20A, 120V, 1.9kW  
**Physical Configuration:** 66 in / 1682 mm, Vertical



**Description:** VSSBN204-102S20TL is ideal for smaller environments that don't have protective surge suppression at the facility level, or just when additional protection is needed. Parallel circuitry keeps the VSSBN204-102S20TL working as a power strip, even if a surge or spike disables surge suppression.

**Product Summary:** VSSBN204-102S20TL, Surge, 20A, 120V, Vertical, (20) NEMA 5-20R, breakered, 10 ft power cord with L5-20P, Black Powder Coat.

**Plug Form:**



L5-20P

**Receptacle:**



NEMA 5-20R  
(Quantity: 20)

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com

## Product Specification and Options:

|                                         |                                         |
|-----------------------------------------|-----------------------------------------|
| Quantity Of Inputs                      | 1                                       |
| Voltage                                 | 120V                                    |
| Current                                 | 20A                                     |
| VA per Input (Load Capacity)            | 1.9kW                                   |
| Frequency                               | 50/60 Hz                                |
| Over Current Protection                 | 20A Thermal Breaker                     |
| Switch                                  | No                                      |
| Indicators - LED(s)                     | 1 - Power ON Green LED                  |
| Power Cable Wire Gauge                  | 12/3                                    |
| Power Cable Length                      | 10ft                                    |
| Plug Type                               | NEMA L5-20P Twistlock                   |
| Receptacle/Socket Type #1               | NEMA 5-20R                              |
| Quantity on Face #1                     | 20                                      |
| Center to Center Receptacle Spacing     | 2.8                                     |
| Quantity per Breaker #1                 | 20                                      |
| Style #1                                | Individual - In-Line                    |
| Maximum Output per Receptacle/Socket #1 | 20A                                     |
| Voltage per Receptacle/Socket #1        | 120V                                    |
| Joule Rating                            | 720                                     |
| UL 1449 Rating (500A)                   | 330V                                    |
| Clamping Level                          | < 315V                                  |
| Response Time                           | < 5 nanoseconds                         |
| Technology Used                         | Super MOVs                              |
| Surge Indicator Red LED                 | Yes                                     |
| Continuous Operating Temperature Range  | 10-45C / 50-113F                        |
| Heavy Steel - Powder Coat Finish        | Black                                   |
| Configuration                           | 66in / 1682mm Vertical Rackmount        |
| Plastic Mounting Clips                  | 1 - Bottom; 2 - Top                     |
| Made in the USA                         | Yes                                     |
| Product Warranty                        | Lifetime (Surge Suppression - 10 Years) |
| Connected Equipment Warranty            | Ten Year - \$10000                      |
| Certification/Agency Approvals          | RoHS Compliant                          |
| Certification/Agency Approvals          | UL & c-UL Listed 60950                  |
| Chassis Dimensions (LxWxD)              | 66.25in x 1.61in x 1.61in               |
| Shipped Weight                          | 9lbs (4.08kg)                           |

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com